

Multi-Device UV Charging Cart, Hospital-Grade, 32 USB Ports, iPad and Android Tablets, Antimicrobial, White

MODEL NUMBER: CSC32USBWHG



Charges, syncs, secures, organizes and sanitizes up to 32 USB devices in healthcare, education, retail, warehouse and office settings.

Features

Mobile Charging Cart Accommodates up to 32 USB Mobile Devices This 120V charging station provides USB charging, secure storage, cord management and surface sanitization for as many as 32 iPad, iPod, iPhone, Android, Surface, Kindle and other USB tablets and smartphones. The USB ports deliver the fastest charging supported by each connected device, up to 2.4A per port. A USB uplink port connects to a host computer for wired syncing. The tablet charging station is recommended for healthcare facilities, classrooms, businesses, government agencies, restaurants, hotels and anywhere else that uses mobile devices on a daily basis.

UV Light Helps Sanitize Devices without Potentially Dangerous Heat, Liquids or Chemicals The CSC32USBWHG helps reduce the presence of germs on Chromebooks, laptops and tablets. Built-in ultraviolet lights help disinfect electronic devices at the touch of a button by destroying most microbes without the use of damaging heat, liquids or chemicals. The germicidal UVC bulbs are on a timer to control the amount of UV exposure the devices receive. An LED on the exterior of the cabinet indicates when the doors are closed and the start button can be pressed to activate the 10-minute timer. A second LED indicates when the UVC lights are on. If a door is opened during sanitization, the lights automatically shut off for safety.

Exclusive, Patented Antimicrobial Protection Fights Surface Bacteria The charging cart's interior and exterior surfaces, including the handle, are protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and viruses, such as C. diff and MRSA. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Locking Steel Enclosure Keeps Valuable Equipment Safe and Secure Constructed from heavy-duty steel, this charging cart provides safe, secure storage. The split front doors lock with the included keys to help prevent theft, damage and tampering. For extra security, the front door can be fastened with a user-supplied padlock. Flow-through ventilation helps protect against overheating, and the specially coated shelves help prevent device scratches and scuffs.

Moving Your Devices from Room to Room Is Easy Four pre-installed swivel casters with large non-marking wheels improve the ride over uneven surfaces, including carpeting and thresholds, and lock to help prevent unwanted movement. The reversible wide-grip handle makes the cart easy to control.

Well-Organized to Avoid Confusing Cable Clutter Cables and connectors run through strain relief bushings, keeping them organized and out of the way, and are protected by blanking panels. Adjustable dividers accommodate up to 16 devices per shelf. Front doors open at least 180 degrees to allow maximum access to the interior. A power cord wrap keeps the input cord out of the way when moving the

Highlights

- 32 internal USB-A ports charge mobile devices with optimum charge level up to 2.4A
- Ultraviolet (UVC) lights help disinfect devices without use of damaging heat or chemicals
- Patented antimicrobial coating is 99.9% effective in inhibiting bacteria and viruses
- Steel enclosure locks with included keys to discourage theft, damage and tampering
- 10-ft. (3.05 m) cord with NEMA 5-15P HG plug allows great flexibility in reaching AC outlets

Applications

- Charge up to 32 Apple, Android, Microsoft, Amazon and other USB tablets and smartphones in medical facilities, schools, businesses and government organizations that rely on the daily use of mobile devices
- Easily and safely transport connected devices from room to room with a smooth, controlled ride
- Sanitize your devices with ultraviolet light to reduce the presence of germs

Package Includes

- CSC32USBWHG Hospital-Grade 32-Device UV Charging Cart, White
- Cart handle
- Input cord wrap



charging station. Access grommets allow the 10-ft. (3.05 m) cord with hospital-grade NEMA 5-15P plug to extend through either side of the cart, allowing great flexibility in reaching AC outlets.

- (12) Hex screws
- Hex key
- (2) Keys
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332240156
Product Type	Multi-Device Charger
Charging Form Factor	Mobile Cart
Functions	Charge; Secure; Sync; Sanitize
Device Compatibility	Tablet; Phone
Device Slots	32
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Charging Ports / Amps	(32) 2.4A
Number of Charging Ports	32
Overcharge Protection	No
Total Charging Amps	80A
Charging Method	USB
Charging Ports Detail	Pass through
Charging Port Type	USB A (FEMALE)
Charging Amps per Port	2.4A
PHYSICAL	
Antimicrobial Coating	Yes
Color	White



Material of Construction	Steel
Shipping Dimensions (hwd / in.)	39.96 x 23.62 x 33.66
Shipping Weight (kg)	70.50
Slot Dimensions - Bottom (hwd / in.)	10.5 x 1.5 x 15.4
Slot Dimensions - Bottom (hwd / mm)	267.3 x 38.2 x 390.5
Slot Dimensions - Top (hwd / in.)	10.5 x 1.5 x 15.4
Slot Dimensions - Top (hwd / mm)	267.3 x 38.2 x 390.5
Unit Dimensions (hwd / cm)	91.69 x 88.39 x 54.86 (with handle installed)
Unit Dimensions (hwd / in.)	36.1 x 34.8 x 21.6 (with handle installed)
Unit Weight (kg)	59.27
Unit Weight (lbs.)	130.67
Number of Shelves	2
ENVIRONMENTAL	
Power Consumption (Watts)	112W
SPECIAL FEATURES	
Cord Management	Yes
EMI/RFI Line Noise Protection	Yes
Locking	Yes
Lock Type	Key; Padlock (User Supplied)
Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to EIA-310-E, FCC & IEC Class B, UL 60950 (Power Component)
Approvals	RoHS
NOM (Mexico)	Tested to NOM (Mexico)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>