

Multi-Device Charging Cart, 36 AC Outlets, Chromebooks and Laptops, 230V, BS 1363, Black

MODEL NUMBER: CSCXB36AC



Keep up to 36 Chromebooks and laptops secure, charged and ready to use.

Features

Charges 36 Chromebooks and Laptops Up to 15 Inches (38.1 cm) 36 AC outlets provide convenient charging for Chromebooks and laptops with a screen size up to 15 inches. This 230V charging station cart also charges tablets and other USB devices through their power adapters. A 3 m AC input cord with a British Standard (BS 1363) plug reaches distant outlets.

Locking Steel Enclosure Keeps Equipment Safe and Secure This locking charging station promotes comprehensive device protection with steel construction and a black powder-coated finish for long-term durability. The front and rear compartments lock with the included keys to help prevent device theft, damage or tampering. For extra security, the front door can be fastened with a user-supplied padlock. Flow-through ventilation helps protect against overheating, and the specially coated shelves help prevent device scratches and scuffs.

Simple Mobility Transport devices from room to room easily with the help of locking swivel casters. The non-marking wheels provide a smooth, even ride, and a reversible wide-grip handle assists with cart control. Corner safety bumpers protect walls and doorways from scratches.

Laminated Wood-Grain Top Serves as a Workstation This charging station features a laminated wood-grain top that serves as a smooth writing surface and can also hold a projector and other devices. You can also mount a television display on your charging station with Tripp Lite's CSC36DM optional display mount adapter kit.

Clutter-Reducing Organization Heavy power adapters store out of the way in removable rear baskets. Cables and connectors run through shelf slots and an overhead cable manager, keeping them organized and out of the way. Adjustable dividers accommodate up to 12 devices per shelf, and the device spaces are numbered for easy identification. A power cord wrap keeps the input cord out of the way when moving the charging station.

2-Year Limited Warranty This charging station cart is backed by Tripp Lite's 2-year limited warranty.

Specifications

Highlights

- Charges 36 Chromebooks and laptops with screen sizes up to 15 inches (38.1 cm)
- Heavy-duty steel construction and locking mechanism keeps equipment secure
- Handle and swivel casters help you safely move connected devices from room to room
- Wood laminate top serves as a workstation
- 3 m AC input cord with British Standard (BS 1363) plug reaches distant outlets

Applications

- Charge up to 36 Chromebooks and laptops in schools, businesses and government organizations that rely on the daily use of mobile devices
- Easily and safely transport connected devices from room to room with a smooth, controlled ride
- Use the laminate top as a workstation or a sturdy platform for A/V equipment

Package Includes

- CSCXB36AC 36-Device AC Charging Station Cart, 230V, BS 1363 Plug and Outlets
- Cart handle
- Input cord wrap
- (6) Protective bumpers
- (10) Hex screws
- Hex key
- (2) Keys
- Owner's manual

OVERVIEW	
UPC Code	037332207098
Product Type	Multi-Device Charger
Charging Form Factor	Mobile Cart
Functions	Charge; Secure
Device Compatibility	Chromebook; Laptop
Device Slots	36
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Voltage Compatibility (VAC)	230
Input Frequency	50 Hz
Input Plug Type	BS1363
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Number of Charging Ports	36
Charging Method	AC
Charging Port Type	BS1363 UK PLUG
Charging Ports Details	Pass through
Charging Ports / Amps	(36) 10A
Overcharge Protection	No
Charging Amps per Port	10A
PHYSICAL	
Color	Black
Material of Construction	Steel
Charging Station Form Factor	Mobile Cart
Shipping Dimensions (hwd / in.)	46.85 x 26.77 x 29.13
Shipping Weight (kg)	77.00
Slot Dimensions - Bottom (hwd / in.)	10.11 x 1.5 x 15.58
Slot Dimensions - Bottom (hwd / mm)	256.9 x 38.22 x 395.72
Slot Dimensions - Middle (hwd / in.)	10.13 x 1.5 x 15.58
Slot Dimensions - Middle (hwd / mm)	257.3 x 38.22 x 395.72

Slot Dimensions - Top (hwd / in.)	10.13 x 1.5 x 15.58
Slot Dimensions - Top (hwd / mm)	257.3 x 38.22 x 395.72
Unit Dimensions (hwd / in.)	40.030 x 24.300 x 23.560
Unit Dimensions (hwd / cm)	107.45 x 71.04 x 56.13 (con la manija instalada)
Unit Weight (lbs.)	110.23
Unit Weight (kg)	50.00
Number of Shelves	3
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Cord Management	Yes
Antimicrobial	No
EMI/RFI Line Noise Protection	No
Locking	Yes
Lock Type	Key
IP68 Rated	No
Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	EN 60950-1; IEC 62368-1; NOM (Mexico)
Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.