

10-Device Desktop USB Charging Station for Tablets, iPads and E-Readers

MODEL NUMBER: CSD1006USB



Locking enclosure provides USB charging, secure storage and cord management for up to 10 tablets, iPads and e-readers. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Description

The CSD1006USB 10-Device Desktop USB Charging Station provides USB charging, secure storage and cord management for up to 10 tablets, iPads and e-readers up to 10.5 inches. It's recommended for schools, offices, warehouses, retail outlets, worksites, healthcare facilities and anywhere else multiple mobile devices are used.

Devices fit into slots 1.25 inches wide and plug into the 10 USB ports as needed for proficient charging. The CSD1006USB delivers up to 5V 2.4A per port, which is plenty of power for charging battery-intensive devices. To protect your devices, the CSD1006USB prevents them from drawing more power than it is capable of supporting and stops charging a device when the device's battery is at 100%.

The CSD1006USB locks with the included keys to help prevent theft, damage or tampering. A cable with combination lock is also included to secure the charging station to a desk, table, cart or other flat surface. The six-foot AC input cord with NEMA 5-15P plug helps you place the charging station in a convenient location. Storage shelf dividers are easily removed to accommodate thicker devices. Cabling is secured beneath the shelf tray to alleviate clutter.

Highlights

- 1.25 in. wide slots hold USB devices up to 10.5 in.
- 6 ft. AC input cord with right-angle NEMA 5-15P plug
- Delivers up to 5V 2.4A per port via BC 1.2 rapid charging
- Locking lid helps prevent device theft, damage or tampering
- Separate cable with combination lock for added security

Package Includes

- CSD1006USB 10-Device Desktop USB Charging Station
- External power supply w/NEMA 5-15P plug (Input: 100–240V, 50/60 Hz; Output: 12V, 8A)
- Enclosure unit with locking lid
- USB charger enclosure mount
- Combination cable lock
- (2) Keys
- Owner's manual



Features

Convenient USB Charging

- 10 USB ports for charging tablets, iPads and e-readers up to 10.5 in.
- Devices fit into slots 1.25 in. wide
- Device USB charge cables plug into USB ports
- 6 ft. AC input cord with right-angle NEMA 5-15P plug reaches convenient outlets
- Recommended wherever multiple mobile devices are used—schools, offices, warehouses, etc.

Comprehensive Protection

- Delivers up to 5V 2.4A per port via BC 1.2 rapid charging
- Protects against overheating, over-current and overcharging

Complete Security

- Locks with included keys to help prevent device theft, damage or tampering
- Included combination cable lock secures the unit to a desk or cart

Clutter-Reducing Organization

- USB ports and cables store out of sight
- Storage shelf dividers can be removed to accommodate thicker devices

Specifications

OVERVIEW	
UPC Code	037332200082
Product Type	Multi-Device Charger
Charging Form Factor	Desktop Cabinet
Functions	Charge; Secure
AC Adapter	Input: 100-240V, 50/60Hz, 2A; Output: 12V, 8A, 6 ft.
Device Compatibility	Laptop; Tablet
Device Slots	10
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83



CHARGING	
Charging Ports / Amps	(10) 2.4A
Number of Charging Ports	10
Overcharge Protection	Yes
Charging Method	USB
Charging Ports Detail	BC 1.2
Charging Port Type	USB A (FEMALE)
Charging Amps per Port	2.4A
PHYSICAL	
Antimicrobial Coating	No
Charging Station Form Factor	Desktop Cabinet
Color	Black; Gray
Material of Construction	Plastic
Shipping Dimensions (hwd / cm)	41.66 x 27.69 x 44.20
Shipping Dimensions (hwd / in.)	16.40 x 10.90 x 17.40
Shipping Weight (kg)	5.62
Shipping Weight (lbs.)	12.40
Unit Dimensions (hwd / cm)	42.01 x 34.39 x 22.71
Unit Dimensions (hwd / in.)	8.94 x 16.54 x 13.54
Number of Shelves	1
ENVIRONMENTAL	
Operating Temperature Range	41 to 95 F (5 to 35 C)
Storage Temperature Range	-4 to 122 F (-20 to 50 C)
Relative Humidity	20% to 80%
FEATURES & SPECIFICATIONS	
Technology	USB
SPECIAL FEATURES	
Cord Management	No
EMI/RFI Line Noise Protection	Yes
Locking	Yes
Lock Type	Key; Combination Cable Lock
Built-In Circuit Breaker	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	No
STANDARDS & COMPLIANCE	
Certifications	EN 55022: 2010/AC: 2011, EN 55024: 2010, FCC Class B, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>