

Industrial Open-Frame Charging Station for 32 Zebra/Handheld devices - USB with Syncing

MODEL NUMBER: CSDO32USBIND



Provides fast charging, convenient syncing, storage and device organization for up to 32 Zebra devices, industrial handhelds, or smartphones in an industrial environment.

Features

Fast Charging for Up to 32 Industrial Handhelds

The CSDO32USBIND features 32 USB-A ports that deliver up to 2.4A apiece to charge devices with USB charging. It stores up to 32 Zebra devices, industrial handhelds, or smartphones with cases up to 7 x 3.65 x 1 inches. For larger devices, there are two large 7.19 x 17.24 x 19.5 inch shelves. Individual shelf dividers and numbered ports keep the devices organized. This charging station is designed for industrial spaces, such as factory floors, warehouses and construction areas, but is also ideal for corporate, healthcare, commercial and retail environments.

Convenient Syncing

A USB uplink port connects to a host computer for wired syncing to update software, back up data and return devices to standard configurations. The CSDO32USBIND also supports wireless syncing and simultaneous syncing/charging (up to 1.5A per port during wired syncing).

Steel Enclosure Keeps Mobile Devices Safe

This charging station is made from durable steel with a black powder-coated finish for long-term durability. Specially coated shelves help prevent device scratches and scuffs.

Firmware Upgrade Ports for Software Upgrades

Mini-USB firmware upgrade ports enable future software upgrades to support newer devices.

Easy to Install

This charging station ships ready for quick, easy installation. Rear-panel slots support wall-mount installation, while the unit is also set up for easy desktop securing.

Highlights

- Built to endure industrial settings, such as factories, warehouses and construction sites
- USB-A ports support 2.4A of fast charging of up to 32 USB devices
- Uplinks to host computer for updating software, backing up data and other syncing
- Supports wireless syncing and simultaneous syncing/charging of devices
- 10 ft. AC input cord with right-angle 5-15P plug allows flexible placing near wall outlet

Package Includes

- CSDO32USBIND 32-Device USB Charging Station
- Detachable AC input cord (10 ft./3 m) with right-angle NEMA 5-15P plug
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332282484
Product Type	Multi-Device Charger



Powering Business Worldwide

TRIPP LITE
SERIES

Charging Form Factor	Stationary Cabinet
Charger Functions	Charge; Secure; Sync
Device Compatibility	Phone
Device Slots	32
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	110; 120
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Frequency Compatibility	50 / 60 Hz
POWER	
Power Consumption (Watts)	112.00
CHARGING	
Number of Charging Ports	32
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Charging Ports / Amps	(32) 2.4A
Overcharge Protection	Yes
Charging Amps per Port	2.4A
PHYSICAL	
Color	Black
Charging Station Form Factor	Stationary Cabinet
Shipping Dimensions (hwd / in.)	21.26 x 21.26 x 26.38
Shipping Dimensions (hwd / cm)	54.00 x 54.00 x 67.01
Shipping Weight (lbs.)	67.00
Shipping Weight (kg)	30.39
Slot Dimensions (hwd / in.)	3.67 x 1.0 x 7.0
Unit Dimensions (hwd / in.)	18.560 x 23.630 x 18.190
Number of Shelves	2



Powering Business Worldwide

TRIPP LITE
SERIES

Assembly Required	No
ENVIRONMENTAL	
Operating Temperature Range	32° to 86°F (0° to 30°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	5% TO 95% RH (NON CONDENSING)
FEATURES & SPECIFICATIONS	
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	Yes
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key
STANDARDS & COMPLIANCE	
Product Certifications	UL 60950-1
Product Compliance	FCC (USA); FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.