

Caster Kit for CST16AC 16-Device AC Charging Station Tower

MODEL NUMBER: CSTCASTERKIT16



Mounts to Tripp Lite CST16AC charging station tower to allow it to be moved from one room to another.

Features

Modify Your Charging Station Tower for Smooth Mobility from Room to Room

This heavy-duty caster set allows you to roll your CST16AC charging station tower from one room to another, rather than mounting it to a wall. The CSTCASTERKIT16 includes four casters (two swiveling) designed for smooth rolling between locations, even through doorways and across carpeting. It also comes with a locking rear door, two handles and a sturdy wood mounting platform with pre-drilled holes for the included mounting hardware.

Highlights

- Optional caster kit provides your charging station tower with mobility
- 4 heavy-duty casters roll smoothly across level floors and through doorways
- Locking rear door helps protect contents against theft, damage or tampering
- Wooden platform features pre-drilled holes for easy mounting with included hardware
- Designed for CST16AC charging station tower

Applications

- Turn a charging station tower into a mobile cart that can be rolled from one position to another

System Requirements

- CST16AC charging station tower

Package Includes

- (4) Metal casters
- Mounting platform
- (2) Handles
- Locking rear door
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332240262
Accessory Type	Rolling Caster Kit
Accessory Class	Charging Station Accessories
INPUT	
Input Connection Type	AC
Voltage Compatibility (VAC)	120
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 5-15P



Powering Business Worldwide



Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Charging Method	AC
Charging Ports / Amps	(20) 15A
PHYSICAL	
Color	White
Charging Station Form Factor	Mobile Cart
Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Shipping Weight (kg)	0.00
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	0
Unit Weight (lbs.)	0
Unit Weight (kg)	0.00
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.