



Powering Business Worldwide

Network Surge Suppressor - Essential protection for TV/VCR coaxial lines

MODEL NUMBER: DCATV



Highlights

- Complete dataline (F coaxial) surge protection
- Protects against the effects of electrostatic discharge
- Lifetime product warranty
- Heavy duty grounding lead

Description

Tripp Lite's DCATV offers type F coax line surge suppression for satellite receivers and broadcast antennas. Convenient coax input and output connections accept standard type F coax wiring. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges. Tripp Lite network surge suppressors reduce blown interface connections by safely shunting dataline surges to ground. Six inch heavy gauge grounding lead connects to designated grounding lugs. Lifetime warranty. **Not for use with cable modems.**
 SUPPRESSION: 1 set type F coax jacks, protects center and shield, 7.5V clamping

Features

- DCATV offers type F coax line surge suppression satellite receivers and broadcast antennas. **Not for use with cable modems.**
- Type F coax input and output connections
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground
- 6 inch heavy gauge grounding lead connects to designated grounding lugs on protected equipment
- Lifetime product warranty

Specifications

OVERVIEW	
UPC Code	037332010889
INPUT	
Recommended Electrical Service	120V, 230V
Input Plug Type	F-Type Coax
Input Cord Length (ft.)	0
Right-Angle Plug	No



Powering Business Worldwide

Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	Network
Circuit Breaker (amps)	750
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	Yes
Network (Ethernet) Protection	No
Additional Dataline Protection	Center & Shield
Telephone/DSL Protection	No
PHYSICAL	
Housing Color	White
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	9.20 x 4.25 x 10.20
Shipping Dimensions (hwd / cm)	23.37 x 10.80 x 25.91
Shipping Weight (lbs.)	1.76
Shipping Weight (kg)	0.80
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 3.000
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.