

Full-Motion Universal Tablet Desk Clamp for 7 in. to 10 in. Tablets

MODEL NUMBER: DDR0710SC



Highlights

- Clamps to most flat surfaces up to 1.6 in. thick
- Fits most tablets ranging from 7 to 10 in.
- Attaches above or below your workspace's surface
- Rotates 360° in portrait and landscape orientations
- Supports up to 2.2 lbs (1 kg)

Package Includes

- DDR0710SC Full-Motion Universal Tablet Desk Clamp
- Installation instructions

Mount your tablet above or below the surface of your desk, table or workstation to free up valuable space. Customize the tablet's angle and height for comfortable viewing.

Description

The DDR0710SC Full-Motion Universal Tablet Desk Clamp attaches to your desk, table or workstation, allowing you to mount your tablet above or below it and free up valuable workspace. Upside-down mounting to a cabinet or workstation lets you read recipes or instructions at eye level. Clamps firmly to most flat surfaces up to 1.6 inches thick. Flexible arm lets you adjust your tablet's angle and height to fit your environment and comfort level. Fits tablets ranging from 7 to 10 inches. Rotates 360°, so you can view your tablet in portrait and landscape orientations. Easy installation in seconds with no tools necessary. Supports tablets up to 2.2 lbs (1 kg).

Features

Attaches to Most Desks, Tables and Workstations

- Clamps securely to most flat surfaces up to 1.6 in. thick
- Fits most tablets from 7 to 10 in.
- Mounts above or below your workspace's surface
- Upside-down mounting lets you read recipes or instructions at eye level
- Flexible arm lets you adjust height and angle for comfortable viewing
- Full 360° rotation in both portrait and landscape orientations

Installs in Seconds

- No tools necessary
- Supports up to 2.2 lbs (1 kg)

Specifications

OVERVIEW

UPC Code	037332190543
Device Compatibility	Tablet
PHYSICAL	
Color	Black
Material of Construction	Metal, Plastic
Motion	Full
Mounting Location	Desk Clamp
Degrees of Motion	-180/+180 Tilt; 360 Swivel; 360 Rotate
Minimum Screen Size (in.)	7
Minimum Screen Size (cm)	17.78
Maximum Screen Size (in.)	10
Maximum Screen Size (cm)	25.4
Maximum Weight Capacity (lbs.)	2.2
Maximum Weight Capacity (kg)	1
Shipping Dimensions (hwd / in.)	3.15 x 8.26 x 11.42
Shipping Dimensions (hwd / cm)	8.00 x 20.98 x 29.01
Shipping Weight (lbs.)	1.72
Shipping Weight (kg)	0.78
Unit Dimensions (hwd / in.)	7.170 x 9.610 x 2.750
Unit Dimensions (hwd / cm)	18.21 x 24.42 x 6.99
Unit Weight (lbs.)	1.28
Unit Weight (kg)	0.58
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Cord Management	No
Antimicrobial	No
Tools Necessary	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2022 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.