

Quad Monitor Mount Stand for 10" to 26" Flat-Screen Displays

MODEL NUMBER: DDR1026MQ



Mounts up to four 10–26 in. monitors on a single base to free up valuable space on your desk, table or workstation. Ideal for home or office use.

Description

The VESA-compliant DDR1026MQ Quad Monitor Mount Stand mounts up to four monitors on a sturdy base, allowing you to free up valuable workspace on your desk, table or workstation. Ideal for home and office, the DDR1026MQ fits most flat-panel displays from 10 to 26 inches.

Position your monitors with one-touch ease to optimize viewing angle and height to fit your environment and comfort level. A 180° swivel and -15° to +15° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitors in portrait or landscape orientation.

Each mount supports up to 30 lbs (13.6 kgs). The durable all-metal frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included.

Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm.

Features

Mounts Up to 4 Monitors on a Base Frees up valuable workspace on your desk, table or workstation Fits most flat-panel displays from 10 to 26 in. Mounts adjust independently for viewing angle Ideal for home and office use

Convenient One-Touch Adjustment 180° swivel and -15° to +15° tilt capability provides comfortable viewing Full 360° rotation for viewing in portrait or landscape orientation

Durable Metal Construction Each mount supports up to 30 lbs (13.6 kgs) Scratch-resistant powder-coated finish blends with any décor Mounting hardware included

VESA Compliance Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm

Specifications

Highlights

- Fits most flat-panel displays from 10 to 26 in.
- One-touch adjustment for comfortable viewing
- 180° swivel and -15° to +15° tilt for wide range of motion
- Each mount supports up to 30 lbs (13.6 kgs)

Package Includes

- Top pole
- Bottom pole
- Base
- (2) Mounting assemblies
- Top cap
- (16) M6 screws
- (16) M4 screws
- (16) Lock washers
- (16) Washers
- (16) Spacers
- Handle and washer
- Hex key, 2.5 mm
- Hex key, 4 mm
- Owner's manual

OVERVIEW	
UPC Code	037332181923
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Full
Mounting Location	Desktop
Degrees of Motion	-15/+15 Tilt; 180 Swivel; 360 Rotate
Minimum Screen Size (in.)	10
Minimum Screen Size (cm)	25.4
Maximum Screen Size (in.)	26
Maximum Screen Size (cm)	66.04
Maximum Weight Capacity (lbs.)	30
Maximum Weight Capacity (kg)	14
Number of Displays	4
Shipping Dimensions (hwd / in.)	5.90 x 31.50 x 12.00
Shipping Dimensions (hwd / cm)	14.99 x 80.01 x 30.48
Shipping Weight (lbs.)	20.90
Shipping Weight (kg)	9.48
Unit Dimensions (hwd / in.)	29.800 x 28.900 x 10.870
Unit Dimensions (hwd / cm)	65.79 x 73.41 x 25.91
Unit Weight (lbs.)	14.00
Unit Weight (kg)	6.35
FEATURES & SPECIFICATIONS	
Cord Management	No
Tools Necessary	Yes
Security Lock	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.