

Quad Monitor Mount Stand for 10" to 26" Flat-Screen Displays

MODEL NUMBER: DDR1026MQ



Mounts up to four 10–26 in. monitors on a single base to free up valuable space on your desk, table or workstation. Ideal for home or office use.

Description

The VESA-compliant DDR1026MQ Quad Monitor Mount Stand mounts up to four monitors on a sturdy base, allowing you to free up valuable workspace on your desk, table or workstation. Ideal for home and office, the DDR1026MQ fits most flat-panel displays from 10 to 26 inches.

Position your monitors with one-touch ease to optimize viewing angle and height to fit your environment and comfort level. A 180° swivel and -15° to +15° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitors in portrait or landscape orientation.

Each mount supports up to 30 pounds. The durable all-metal frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm.

Features

Mounts Up to 4 Monitors on a BaseFrees up valuable workspace on your desk, table or workstationFits most flat-panel displays from 10 to 26 in.Mounts adjust independently for viewing angleIdeal for home and office use

Convenient One-Touch Adjustment180° swivel and -15° to +15° tilt capability provides comfortable viewingFull 360° rotation for viewing in portrait or landscape orientation

Durable Metal ConstructionEach mount supports up to 30 lb.Scratch-resistant powder-coated finish blends with any décorMounting hardware included

VESA ComplianceSupports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm

Highlights

- Fits most flat-panel displays from 10 to 26 in.
- One-touch adjustment for comfortable viewing
- 180° swivel and -15° to +15° tilt for wide range of motion
- Each mount supports up to 30 lb.

Package Includes

- Top pole
- Bottom pole
- Base
- (2) Mounting assemblies
- Top cap
- (16) M6 screws
- (16) M4 screws
- (16) Lock washers
- (16) Washers
- (16) Spacers
- Handle and washer
- Hex key, 2.5 mm
- Hex key, 4 mm
- Owner's manual

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--------------------------------------|--------------------------------------|
| UPC Code | 037332181923 |
| Device Compatibility | Monitor/HDTV |
| PHYSICAL | |
| Color | Black |
| Degrees of Motion | -15/+15 Tilt; 180 Swivel; 360 Rotate |
| Material of Construction | Steel |
| Maximum Screen Size (cm) | 66.04 |
| Maximum Screen Size (in.) | 26 |
| Maximum Weight Capacity (kg) | 14 |
| Maximum Weight Capacity (lbs.) | 30 |
| Minimum Screen Size (cm) | 25.4 |
| Minimum Screen Size (in.) | 10 |
| Motion | Full |
| Mounting Location | Desktop |
| Number of Displays | 4 |
| Shipping Dimensions (hwd / cm) | 14.99 x 80.01 x 30.48 |
| Shipping Dimensions (hwd / in.) | 5.90 x 31.50 x 12.00 |
| Shipping Weight (kg) | 9.48 |
| Shipping Weight (lbs.) | 20.90 |
| Unit Dimensions (hwd / cm) | 65.79 x 73.41 x 25.91 |
| Unit Dimensions (hwd / in.) | 25.9 x 28.9 x 10.2 |
| Unit Weight (kg) | 6.35 |
| Unit Weight (lbs.) | 14.00 |
| VESA Pattern (mm) | 100x100; 100x75; 75x100; 75x75 |
| FEATURES & SPECIFICATIONS | |
| Tools Necessary | Yes |
| SPECIAL FEATURES | |
| Cord Management | No |
| Security Lock | No |
| STANDARDS & COMPLIANCE | |
| Approvals | RoHS3, REACH |
| WARRANTY | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|-------------------------|
| Product Warranty Period (Worldwide) | 5-year limited warranty |
|--|-------------------------|

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>