

Single Monitor Mount Stand for 10" to 32" Flat-Screen Displays

MODEL NUMBER: DDR1032SE



Mounts your monitor on a base to free up valuable space on your desk, table or workstation. Ideal for home or office use.

Description

The VESA-compliant DDR1032SE Single Monitor Mount Stand mounts your monitor on a sturdy base, allowing you to free up valuable workspace on your desk, table or workstation. Ideal for home and office, the DDR1032SE fits most flat-panel displays from 10 to 32 inches.

Position your monitor with one-touch ease to optimize viewing angle and height to fit your environment and comfort level. A 180° swivel and -15° to +15° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitor in portrait or landscape orientation.

Mount supports up to 36 lbs (16.3 kgs). The durable all-metal frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm.

Features

Mounts Your Monitor on a Base Frees up valuable workspace on your desk, table or workstation Fits most flat-panel displays from 10 to 32 in. Mount adjusts independently for viewing angle and height Ideal for home and office use

Convenient One-Touch Adjustment 180° swivel and -15° to +15° tilt capability provides comfortable viewing Full 360° rotation for viewing in portrait or landscape orientation

Durable Metal Construction Mount supports up to 36 lbs (16.3 kgs) Scratch-resistant powder-coated finish blends with any décor Mounting hardware included

VESA Compliance Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm

Highlights

- Fits most flat-panel displays from 10 to 32 in.
- One-touch adjustment for comfortable viewing
- 180° swivel and -15° to +15° tilt for wide range of motion
- Supports up to 36 lbs (16.3 kgs)

Package Includes

- Pole
- Base
- Mounting assembly
- Top cap
- (4) M6 screws
- (4) M4 screws
- (4) M6 lock washers
- (4) Washers
- (4) Spacers
- (2) Hex keys
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332181763



Powering Business Worldwide



Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Full
Mounting Location	Desktop
Degrees of Motion	-15/+15 Tilt; 180 Swivel; 360 Rotate
Minimum Screen Size (in.)	10
Minimum Screen Size (cm)	25.4
Maximum Screen Size (in.)	32
Maximum Screen Size (cm)	81.28
Maximum Weight Capacity (lbs.)	36
Maximum Weight Capacity (kg)	16
Number of Displays	1
Shipping Dimensions (hwd / in.)	6.60 x 11.60 x 18.40
Shipping Dimensions (hwd / cm)	16.76 x 29.46 x 46.74
Shipping Weight (lbs.)	9.30
Shipping Weight (kg)	4.22
Unit Dimensions (hwd / in.)	15.160 x 16.770 x 10.100
Unit Dimensions (hwd / cm)	39.88 x 25.91 x 37.8
Unit Weight (lbs.)	5.50
Unit Weight (kg)	2.49
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.