



Powering Business Worldwide



## Full-Motion Desk Mount for 13" to 27" Flat-Screen Displays

MODEL NUMBER: **DDR1323S**

### Description

Tripp Lite's sleekly designed, VESA-compliant DDR1323S Full-Motion Flat-Screen Desk Mount frees up valuable space in your workstation and allows you to re-position your display for increased viewing comfort and improved ergonomics. It features convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 13- to 27-inch flat-panel displays. Its durable, all-metal frame with soft, rubber feel finish withstands the stress of repeated use and blends easily into any décor. It comes with all necessary mounting hardware and supports weights of up to 20 lbs. For peace of mind, the DDR1323S comes backed by a 5-year warranty.

### Features

- Tripp Lite's sleekly designed, VESA-compliant DDR1323S Full-Motion Flat-Screen Desk Mount frees up valuable space in your workstation and allows you to re-position your display for increased viewing comfort and improved ergonomics
- Convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 13- to 27-inch flat-panel displays
- Durable, all-metal frame with soft, rubber feel finish withstands the stress of repeated use and blends easily into any décor
- Includes all necessary mounting hardware and supports weights of up to 20 lbs
- 5-year warranty

### Highlights

- **SEE NEW MODEL - DDR1327S**
- Increases available desk/table space in office workstation applications
- Fits most flat-panel displays from 13" to 27"
- Convenient one-touch display adjustment for easy view optimization and improved ergonomics
- Full range of motion with -40° to +90° tilt, 180° swivel and 360° rotation capability
- Supports up to 20 lbs.
- 5-year warranty

### Package Includes

- DDR1323S Full-Motion Flat-Screen Desk Mount
- Mounting Hardware
- Owner's Manual

## Specifications

OVERVIEW	
UPC Code	037332178701
PHYSICAL	
Color	Black
Material of Construction	Metal
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Desktop
Degrees of Motion	-40/+90 Tilt; 180 Swivel; 360 Rotate
Maximum Weight Capacity (lbs.)	20
Maximum Weight Capacity (kg)	9
Min/Max Arm Extension (in.)	19.68
Min/Max Arm Extension (cm)	50
Shipping Dimensions (hwd / in.)	5.39 x 15.79 x 16.73
Shipping Dimensions (hwd / cm)	13.69 x 40.11 x 42.49



Powering Business Worldwide



Shipping Weight (lbs.)	11.55
Shipping Weight (kg)	5.24
Unit Dimensions (hwd / in.)	20.070 x 6.300 x 23.700
Unit Weight (lbs.)	11.55
Unit Weight (kg)	5.24
FEATURES & SPECIFICATIONS	
Cord Management	Yes
Tools Necessary	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.