

Dual-Monitor Desktop Mount Stand for 13" to 27" Flat-Screen Displays

MODEL NUMBER: DDR1327SDD



Full-motion desktop stand mounts 2 flat-screen monitors on independently adjustable arms and a single base to free up valuable space on your desk, table or workstation. Recommended for home or office use.

Description

The VESA-compliant DDR1327SDD Dual Flat-Screen Monitor Desktop Mount Stand mounts two flat-screen monitors on a sturdy base, allowing you to free up valuable workspace on your desk, table or workstation. Recommended for home or office, the DDR1327SDD fits most flat-panel displays from 13 to 27 inches.

Position your monitors with one-touch ease to optimize viewing angle and height to fit your environment and comfort level. A 180° swivel and -45° to +45° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitors in portrait or landscape orientation.

Each VESA mount supports up to 26 lbs (11.8 kgs). The durable steel frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with either of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm.

Features

Mounts 2 Flat-Screen Monitors on a Sturdy Base Fits most flat-panel TVs, monitors and other displays from 13 to 27 in. Frees up valuable workspace on your desk, table or workstation. Mounting arms adjust independently for viewing angle. Ideal for home or office use.

Convenient One-Touch Adjustment 180° swivel and -45° to +45° tilt capability provide comfortable viewing. Full 360° rotation for viewing in portrait or landscape orientation.

Durable Steel Construction Each mount supports up to 26 lbs (11.8 kgs). Scratch-resistant powder-coated finish blends with any décor. Mounting hardware included.

VESA Compliance Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm.

Specifications

Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- Rotates 360° for viewing in portrait or landscape orientation
- 180° swivel and -45° to +45° tilt for wide range of motion
- Supports up to 26 lbs (11.8 kgs) per VESA mount

Package Includes

- Pole
- Base
- (2) Mounting arms
- Locking head assembly
- Pole cable guide
- Base collar
- (2) VESA plate assemblies
- (2) Arm cable guides
- (2) End caps
- (8) Washers
- (18) Screws
- Hex key, 3 mm
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual

OVERVIEW	
UPC Code	037332203397
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Full
Mounting Location	Desktop
Degrees of Motion	-45/+45 Tilt; 180 Swivel; 360 Rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	26
Maximum Weight Capacity (kg)	12
Number of Displays	2
Shipping Dimensions (hwd / in.)	12.83 x 18.11 x 5.20
Shipping Dimensions (hwd / cm)	32.59 x 46.00 x 13.21
Shipping Weight (lbs.)	12.76
Shipping Weight (kg)	5.79
Unit Dimensions (hwd / in.)	18.110 x 31.690 x 10.000
Unit Dimensions (hwd / cm)	46.0 x 80.5 x 25.4
Unit Weight (lbs.)	10.56
Unit Weight (kg)	4.79
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Cord Management	Yes
Antimicrobial	No
Tools Necessary	Yes
Security Lock	No
Height Adjustable	No
STANDARDS & COMPLIANCE	

TRIPP-LITE

by **EATON**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

TRIPP-LITE

by **EATON**

© 2022 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.