

Dual Full Motion Flex Arm Desk Clamp for 13" to 27" Monitors

MODEL NUMBER: DDR1327SDFC



Mounts 2 monitors off the surface of your desk, table or workstation to free up valuable space. Tilts from -15° to +15°. Ideal for home or office use.

Description

The VESA-compliant DDR1327SDFC Dual Full Motion Flex Arm Desk Clamp attaches to your desk, table or workstation, allowing you to mount two monitors above it and free up valuable workspace. Ideal for home and office, the DDR1327SDFC fits most flat-panel displays from 13 to 27 inches.

Dual swivel arms can be independently adjusted for angle to give you maximum flexibility in positioning your monitors to fit your environment and comfort level. Move a screen closer to you, or push both screens out of your way when not in use. A 180° swivel and -15° to +15° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitors in portrait or landscape orientation.

Durable clamp attaches to most flat surfaces up to 3.5 inches thick for a firm grip, or install it using a desk hole up to 2.75 inches in diameter. Each swivel arm supports up to 22 pounds. The durable all-metal frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm.

Features

Attaches to Most Desks, Tables and Workstations

- Clamps securely to most flat surfaces from 0.4 in. to 3.5 in.
- Fits most flat-panel displays from 13 to 27 in.
- Dual swivel arms adjust independently for angle
- Ideal for home and office use

Convenient One-Touch Adjustment

- 180° swivel and -15° to +15° tilt capability provides comfortable viewing from multiple angles
- Full 360° rotation for viewing in portrait or landscape orientation

Durable Metal Construction

Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- 180° swivel and -15° to +15° tilt for wide range of motion
- Each swivel arm supports up to 22 lb.

Package Includes

- Adapter bracket assembly
- Pole
- Desk clamp assembly
- (8) M4 screws
- (8) M5 screws
- (8) D5 washers
- Base plate
- Pad
- Hex key, 3 mm
- Hex key, 4 mm
- Owner's manual



- Each swivel arm supports up to 22 lb.
- Scratch-resistant powder-coated finish blends with any décor
- Mounting hardware included
- Display cables attach to mount to reduce clutter

VESA Compliance

- Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm

Specifications

OVERVIEW	
UPC Code	037332184863
PHYSICAL	
Color	Black
Degrees of Motion	-15/+15 Tilt; 180 Swivel; 360 Rotate
Material of Construction	Steel
Maximum Screen Size (cm)	68.58
Maximum Screen Size (in.)	27
Maximum Weight Capacity (kg)	10
Maximum Weight Capacity (lbs.)	22
Minimum Screen Size (cm)	33.02
Minimum Screen Size (in.)	13
Motion	Full
Mounting Location	Desk Clamp
Number of Displays	2
Shipping Dimensions (hwd / cm)	22.86 x 20.83 x 45.21
Shipping Dimensions (hwd / in.)	9.00 x 8.20 x 17.80
Shipping Weight (kg)	4.90
Shipping Weight (lbs.)	10.80
Unit Dimensions (hwd / cm)	51 x 85,39 x 11,51
Unit Dimensions (hwd / in.)	20.08 x 33.63 x 4.53
Unit Weight (kg)	3.49
Unit Weight (lbs.)	7.7
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	Yes
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>