

Single-Display Monitor Arm with Desk Clamp and Grommet - Height Adjustable, 17" to 32" Monitors

MODEL NUMBER: DDR1732SC



Mounts one monitor to your workspace using either clamp or grommet and allows one-touch vertical adjustment via easy-grip knob.

Features

Low-Profile Monitor Desk Mount Makes It Easy to Adjust the Height of Your Monitor Adjusting the height of desktop flat-panel displays at home or the office often requires a lot of effort - loosening fasteners, moving the monitor up and down, tightening knobs to secure the monitor in place. With the DDR1732SC, all it takes is a simple turn of the easy-grip knob on the back of the vertical support for fast one-touch adjustment from 10.2 to 17.7 inches. The monitor arm is compatible with flat-panel screens ranging from 17 to 32 inches.

Choose Clamp or Grommet Mounting to Match Your Preference This monitor mount includes a clamp for attaching it to the edge of a desk or table and a grommet for secure mounting through the desktop. The clamp supports surfaces ranging from 0.4 to 1 inch thick. Grommet mounting works with surfaces from 0.4 to 1.6 inches thick. Maximum weight capacity is 17.6 pounds (7.9 kg). Cables are efficiently wrangled through the rear of the arm to keep them organized.

Swivel, Tilt and Rotate the Screen to Find the Perfect and Most Comfortable Viewing Angle This monitor-arm desk mount adjusts independently to optimize viewing angles and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features -10° to +10° tilt, 10° swivel and 180° rotation for position your screen in portrait or landscape orientation. Easy screen adjustment lets you quickly find just the right angle without interrupting your workday. The slim design makes this single-monitor mount ideal for sit-stand workstations.

VESA-Compliant Mounting Ensures Display Compatibility VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100. Mounting hardware is included.

Sure to Stand Up to Frequent Use The durable steel frame withstands the stress of repeated adjustments. Its scratch-resistant powder-coated finish tolerates frequent handling and blends easily into any home or office décor.

Highlights

- Low-profile monitor arm attaches to your desktop with either clamp or grommet mount - .4 to 1" for clamp and .4 to 1.6" for grommet.
- One-touch adjustment lets you view the monitor at a comfortable height
- Offers -10° to +10° tilt, 10° swivel and 180° rotation to help you find the perfect angle
- Durable steel construction blends into any décor and supports up to 17.6 lbs (7.9 kgs)
- Display cables attach to slim mount to reduce clutter and keep cords organized

Applications

- Adjust the height of your desk monitor with just a twist of a knob, instead of loosening and tightening multiple fasteners and handles
- Mount a monitor to your sit-stand desk or workstation without taking up much valuable surface space
- Swivel, tilt and/or rotate your screen for the most comfortable viewing angle

Package Includes

- DDR1732SC Single-Display Monitor Arm, 17" to 32" Monitors
- Mounting hardware
- Owner's manual

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332248893
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 75x75
Motion	Swivel; Tilt
Mounting Location	Desk Clamp
Degrees of Motion	-10/+10 Tilt and Swivel; 360 Rotate
Minimum Screen Size (in.)	17
Minimum Screen Size (cm)	43.18
Maximum Screen Size (in.)	32
Maximum Screen Size (cm)	81.28
Maximum Weight Capacity (lbs.)	17.6
Maximum Weight Capacity (kg)	8
Number of Displays	1
Shipping Dimensions (hwd / in.)	16.00 x 5.10 x 3.50
Shipping Dimensions (hwd / cm)	40.64 x 12.95 x 8.89
Shipping Weight (lbs.)	5.10
Shipping Weight (kg)	2.31
Unit Dimensions (hwd / in.)	20.900 x 5.900 x 4.600
Unit Dimensions (hwd / cm)	53.0 x 15.0 x 11.6
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	5-year limited warranty
----------------------------------------	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.