

## Safe-IT Precision-Placement Desktop Mount with Antimicrobial Tape for 17 to 32-inch Displays

MODEL NUMBER: DDV1732AM



Steel desk mount adjusts your 17 to 32 in. monitor to a comfortable height to free up valuable space on your desk or work area.

### Features

#### Desktop Monitor Mount Lifts Your Display Above Your Work Area's Surface

This Safe-IT™ desk mount raises your display above your desk, table or workstation, allowing you to free up valuable surface space. Recommended for home or office use, the DDV1732AM fits most flat-screen and curved-screen monitors from 17 to 32 inches. The durable steel frame and handle tolerate frequent adjustments, and the premium coil spring supports displays up to 15.4 pounds (7 kilograms). All hardware is included.

#### Swivel, Tilt and Rotate the Dual Screens to Find the Most Comfortable Viewing Angles

The premium coil spring adjusts effortlessly to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features tilt, swivel and 360° rotation for positioning your screens. Easy screen adjustment lets you quickly find just the right angles without interrupting your workday.

#### VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for television sets and monitors. For hassle-free display compatibility, this desktop monitor stand supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100. Monitor cables route through a slot to eliminate clutter and keep cords hidden and organized.

#### Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Environment

The DDV1732AM comes with a strip of antimicrobial tape, which you can apply to the handle for additional protection against the growth of bacteria, viruses, fungi, mold and mildew.

## Specifications

### Highlights

- Premium coil spring allows effortless adjustment with the featured handle
- Adjustable steel mount supports most 17–32 in. monitors up to 15.4 lb.
- Tilt, swivel and 360° rotation for portrait or landscape help you find the perfect angle
- Display cables route through convenient slot to eliminate messy cord clutter
- Includes antimicrobial tape for the handle to help protect against bacteria and viruses

### System Requirements

Flat-screen or curved-screen televisions or monitors from 17 to 32 in.

### Package Includes

- DDV1732AM Precision-Placement Desktop Mount
- Antimicrobial tape
- Assembly hardware
- Owner's manual

### OVERVIEW

UPC Code

037332268259



Device Compatibility	Laptop; Monitor/HDTV
<b>PHYSICAL</b>	
Material of Construction	Steel
Color	Black
VESA Pattern (mm)	75x75; 100x100
Antimicrobial	Yes
Motion	Full
Mounting Location	Desktop
Degrees of Motion	-15/+15 Tilt; +/-40 Swivel
Minimum Screen Size (in.)	17
Minimum Screen Size (cm)	43.18
Maximum Screen Size (in.)	32
Maximum Screen Size (cm)	81.28
Maximum Weight Capacity (lbs.)	15.4
Maximum Weight Capacity (kg)	7
Number of Displays	1
Unit Dimensions (hwd / in.)	22.4 x 9.45 x 7.87
Unit Dimensions (hwd / cm)	56.9 x 24 x 19.9
Unit Weight (lbs.)	6.5
Unit Weight (kg)	2.95
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	RoHS3, REACH and CE
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>