


Mobile Workstation with Monitor Mount - For 17" to 32" Displays, Height Adjustable

MODEL NUMBER: DMCS1732S



Mobile desk with monitor mount is an all-in-one workstation you can roll from room to room. Height adjustments provide optimal comfort.

Features

Roll This All-in-One Adjustable-Height Workstation Wherever You Need to Go This workstation with monitor mount has four swivel casters, so you can roll it wherever your work takes you. The placement of the monitor and keyboard tray are adjustable, so you can use the DMCS1732S as a standing desk or a sitting workspace at home, school or the office. Because of its small footprint, the workstation fits in spaces too small for a traditional desk. When not in use, the workstation can be rolled into a secure area for storage. Two of the casters lock to prevent unwanted movement.

Easily Mount a 17" to 32" Display and Adjust the Viewing Angle For hassle-free display compatibility, this rolling cart supports 75 x 75, 75 x 100, 100 x 75 and 100 x 100 VESA mounting hole patterns for flat-panel displays from 17 to 32 inches. Maximum supported weight is 17.6 lbs (7.9 kgs). Depending on where it is secured to the steel support pole, the monitor mount can provide a viewing height anywhere from 37 to 68.9 inches above the floor. The mount offers -15° to +15° tilt adjustment to improve the viewing angle. It also has ±180° rotation.

Move the Keyboard Tray to a Comfortable Height The keyboard tray adjusts from 34.8 to 66.7 inches above the floor. To raise or lower the tray, simply loosen the adjustment knobs, move the tray to the desired height and tighten the knobs. The keyboard tray has a wrist rest and plenty of room for the included mouse pad. It supports up to 4.4 lbs (1.9 kgs). A cable manager keeps keyboard and mouse cables separated and untangled. The support pole has two guides for neatly routing all cables toward the bottom of the workstation.

Adjust the CPU Holder to Accommodate Different Form Factors To accommodate a variety of form factors, the CPU holder's width adjusts from 4.8 to 8.3 inches. You can also adjust the height of the holder from 4.4 to 28.8 inches above the floor. The holder supports up to 22 lbs (9.9 kgs) and includes straps to secure a CPU or other component.

Specifications

OVERVIEW

Highlights

- Accommodates most flat-panel displays from 17 to 32 in. and up to 17.6 lbs (7.9 kgs)
- Monitor mount adjusts from 37 to 68.9 inches above the floor
- -15° to +15° tilt adjustment improves viewing angles
- Keyboard tray and CPU holder are height adjustable for user comfort
- Swivel casters allow easy rolling over thresholds

Applications

- Give a presentation at a trade show booth
- Input patient information from multiple exam rooms in a clinic
- Take inventory in a large warehouse
- Deliver a lecture or a daily lesson to students in different classrooms
- Set up an efficient workstation for a temporary employee

Package Includes

- All DMCS1732S components (assembly required)
- Assembly fasteners
- Display mounting fasteners
- Hex keys
- Wrench
- Mouse pad
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332239440
Device Compatibility	Monitor/HDTV
PHYSICAL	
Material of Construction	Steel
Color	Black
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Tilt
Mounting Location	Floor
Degrees of Motion	-30° to +30°
Minimum Screen Size (in.)	17
Minimum Screen Size (cm)	43.18
Maximum Screen Size (in.)	32
Maximum Screen Size (cm)	81.28
Maximum Weight Capacity (lbs.)	18
Maximum Weight Capacity (kg)	8
Number of Displays	1
Shipping Dimensions (hwd / cm)	17.02 x 52.58 x 107.95
Shipping Dimensions (hwd / in.)	6.70 x 20.70 x 42.50
Shipping Weight (kg)	14.74
Shipping Weight (lbs.)	32.50
Unit Dimensions (hwd / in.)	70.1 x 25.7 x 21
Unit Dimensions (hwd / cm)	178.1 x 65.28 x 53.34
Unit Weight (lbs.)	22.7
Unit Weight (kg)	10.30
FEATURES & SPECIFICATIONS	
Cord Management	No
Tools Necessary	Yes
Security Lock	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>