

Rolling TV/Monitor Cart - for Flat/Curved 32" to 70" TVs and Monitors

MODEL NUMBER: **DMCS3270XP**



Height-adjustable mobile TV stand hangs a flat- or curved-panel television or monitor and peripherals, such as a Blu-ray player, laptop and webcam.

Description

The DMCS3270XP Mobile TV Cart allows you to mount a flat- or curved-panel television, monitor or other display and move it from room to room for best viewing or against a wall out of the way when not in use. Recommended for classrooms, lecture halls, offices, auditoriums and conference rooms, the height-adjustable mobile stand fits most displays from 32 to 70 inches.

You can adjust this heavy-duty rolling TV stand's height from 47 to 81.5 inches. You can also rotate the display for viewing in portrait or landscape modes. Roll the unit with little effort to the proper viewing location and angle on sturdy three-inch swivel casters that move smoothly through doorways and over thresholds. All four casters lock to keep the stand securely in position.

A shelf mounted above the display holds projectors, webcams and laptops. A lower shelf supports up to 11 lbs (4.9 kgs) and holds other audio/video components, such as a Blu-ray player. Durable aluminum and steel construction supports up to 150 lbs (68 kgs). The adapter brackets can be adjusted to conform to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300 and 600 x 400

Features

Height Adjustable Display Stand Rolls from Room to Room Mobile mount for flat/curved-panel TVs, monitors and other displays Recommended for classrooms, lecture halls, offices, auditoriums and conference rooms Fits most displays from 32 to 70 in.

Flexible Features That Meet Your Specifications Height adjusts from 47 to 81.5 in. Rotates for viewing in portrait or landscape modes

Rolls on Sturdy Metal Casters 3 in. swivel casters move smoothly through doorways and over thresholds All casters lock to hold stand securely in position while at rest

Durable Construction Made from aluminum and steel Upper shelf holds projectors, webcams and laptops Lower shelf holds A/V components, such as Blu-ray player Supports up to 150 lbs (68 kgs) Laptop shelf holds up to 11 lbs (4.9 kgs)

VESA Compliance Supports the following VESA mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400,

Highlights

- Fits most flat or curved panel displays from 32 to 70 in.
- Designed for portrait or landscape mounting
- Height adjusts from 47 to 81.5 in.
- Locking 3 in. swivel casters for easy movement
- Supports up to 150 lbs (68 kgs) Laptop shelf holds up to 11 lbs (4.9 kgs)

Package Includes

- Middle base
- Left leg
- Right leg
- Left cover
- Right cover
- Support plate
- Universal plate
- (2) Plastic covers
- (2) Adapter brackets
- Column
- Plastic handle
- Top cover
- Connecting plate
- Camera shelf
- DVD shelf
- (8) Washers
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M8 x 20 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (8) M6 x 16 screws
- (3) M6 x 25 screws
- (7) M4 x 6 screws
- (2) M6 x 14 screws
- (6) M6 x 8 screws
- (4) M8 x 25 screws
- (2) M5 x 8 screws
- (8) Small spacers
- (8) Big spacers

600 x 300 and 600 x 400

- Allen wrench
- Wrench
- Owner's manual

Specifications

| OVERVIEW | |
|---------------------------------|--|
| UPC Code | 037332203328 |
| Device Compatibility | Monitor/HDTV; Projector |
| PHYSICAL | |
| Color | Black; Silver |
| Material of Construction | Aluminum, Steel |
| VESA Pattern (mm) | 200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400 |
| Motion | Full |
| Mounting Location | Floor |
| Degrees of Motion | 360° Rotate |
| Minimum Screen Size (in.) | 32 |
| Minimum Screen Size (cm) | 81.28 |
| Maximum Screen Size (in.) | 70 |
| Maximum Screen Size (cm) | 177.8 |
| Maximum Weight Capacity (lbs.) | 150 |
| Maximum Weight Capacity (kg) | 68 |
| Number of Displays | 1 |
| Shipping Dimensions (hwd / in.) | 9.65 x 20.87 x 44.72 |
| Shipping Dimensions (hwd / cm) | 24.51 x 53.01 x 113.59 |
| Shipping Weight (lbs.) | 59.00 |
| Shipping Weight (kg) | 26.76 |
| Unit Dimensions (hwd / in.) | 81.500 x 32.600 x 27.600 |
| Unit Weight (lbs.) | 46.2 |
| Unit Weight (kg) | 20.96 |
| Assembly Required | Yes |
| FEATURES & SPECIFICATIONS | |
| Antimicrobial | No |

| | |
|-------------------------------------|-------------------------|
| Cord Management | No |
| Tools Necessary | Yes |
| Security Lock | No |
| Built-in Cable Management | No |
| Casters | Yes |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |