

Rolling TV/Monitor Cart - for 37" to 70" TVs and Monitors - Classic Edition

MODEL NUMBER: **DMCS3770L**



Mobile TV stand lets you roll a mounted flat-panel display and its components from room to room on metal casters.

Features

Move Your Flat-Panel Display and Components Wherever You Want ThemThe DMCS3770L Rolling TV Stand allows you to install a flat-panel television or monitor and its components (Blu-ray player, laptop, webcam, DVR), and then roll them safely and smoothly from room to room or from one corner of the room to another. The rolling TV stand is recommended for classrooms, lecture halls, offices, auditoriums, conference rooms and other settings where you need your audio/video equipment to be mobile. Supports up to 88 lbs (39.9 kgs)

Designed to Match a Wide Variety of ApplicationsThe height-adjustable mobile TV floor stand fits most LCD, plasma and other flat-panel displays from 37 to 70 inches. Its durable aluminum and steel frame supports up to 88 lbs (39.9 kgs). You can raise or lower the height of the display from 52.5 to 67.5 inches above the floor, and adjust the display to an appropriate viewing angle from -10° to +10°.

Rolls Easily from Place to Place on Sturdy Metal CastersThe mobile TV cart with wheels rolls almost effortlessly to the proper viewing location and angle on sturdy four-inch swivel casters with rubber wheels that move smoothly in any direction through doorways and over thresholds. The rear casters lock to keep the stand securely in position while at rest. Equipment cables route through the stand's telescoping poles to keep them organized and out of the way during transport.

Convenient Shelf Holds Components in PlaceA height-adjustable shelf mounted below the display holds various audio/video components, such as a Blu-ray player, laptop, webcam, cable box, DVR or video game system. The shelf measures 11 x 19 inches and supports up to 22 lbs (9.9 kgs).

Complies with VESA StandardsThe DMCS3770L conforms to VESA-compliant displays with any of the following standard mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 300, 500 x 400, 600 x 300 and 600 x 400.

5-Year Warranty and Environmentally Responsible DesignThe DMCS3770L comes with a 5-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Accepts most popular flat-panel displays from 37 to 70 in.
- Moves easily through doorways and over thresholds on durable metal casters
- Display adjusts in height from 52.5 to 67.5 in. for most comfortable viewing angle
- Adjustable shelf holds laptop, Blu-ray player, webcam and other necessary components
- Sturdy aluminum and steel construction built to withstand frequent movement
- Supports up to 88 lbs (39.9 kgs)

Applications

- Mount a large flat-screen television and Blu-ray player for showing promotional videos at trade shows
- Roll a TV/Blu-ray player combo from classroom to classroom for sharing educational videos with students
- Attach a webcam to a flat-screen monitor for teleconferencing in corporate boardrooms

Package Includes

- Left leg
- Right leg
- Left cover
- Right cover
- Middle base
- (2) Front casters
- (2) Locking rear casters
- (2) Telescoping poles
- (6) Hole covers
- Universal plate
- DVD shelf
- (2) Brackets
- (2) Mounting arms
- (2) Shelf screw covers
- Assorted hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332213471
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Aluminum, Steel
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x300; 500x400; 600x300; 600x400
Motion	Tilt
Mounting Location	Floor
Degrees of Motion	-10° to +10°
Minimum Screen Size (in.)	37
Minimum Screen Size (cm)	93.98
Maximum Screen Size (in.)	70
Maximum Screen Size (cm)	177.8
Maximum Weight Capacity (lbs.)	88
Maximum Weight Capacity (kg)	40
Number of Displays	1
Shipping Dimensions (hwd / in.)	3.10 x 19.10 x 40.80
Shipping Dimensions (hwd / cm)	7.87 x 48.51 x 103.63
Shipping Weight (lbs.)	38.20
Shipping Weight (kg)	17.33
Unit Dimensions (hwd / in.)	67.500 x 27.600 x 27.900
Unit Weight (lbs.)	35.50
Unit Weight (kg)	16.10
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
Built-in Cable Management	No

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Casters	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.