

Rolling TV/Monitor Cart for 37" to 70" Flat-Screen Displays, Rotating Portrait/Landscape Mount

MODEL NUMBER: DMCS3770ROT



Heavy-duty mobile TV/monitor stand with rotatable mount allows one-touch transitions between portrait and landscape modes.

Features

Height Adjustable Display Stand Rolls from Room to Room Mobile mount for flat panel TVs, monitors and other displays Recommended for classrooms, lecture halls, offices, auditoriums and conference rooms Fits most displays from 37 to 70 in.

Flexible Features That Meet Your Specifications 5 degree tilt provides an ergonomic writing position Rotates for viewing in portrait or landscape modes

Rolls on Sturdy Metal Casters 4 in. swivel casters move smoothly through doorways and over thresholds All casters lock to hold stand securely in position while at rest

Durable Construction Made from steel Lower shelf holds A/V components, such as Blu-ray player Supports up to 154 lb. Laptop shelf holds up to 11 lbs.

VESA Compliance Supports the following VESA mounting hole patterns: 200 x 200, 300 x 300, 350 x 350, 400 x 200, 400 x 400, 600 x 200 and 600 x 400

Highlights

- Supports most flat-panel monitors and interactive displays from 37 to 70 in.
- Mount rotates 90° with a single touch for portrait or landscape viewing; no tools needed
- Heavy-duty casters enable smooth rolling and lock to secure the cart at rest
- +5° tilt offers an ergonomic angle for writing on a whiteboard or interactive display
- Supports screens up to 154 lb. Laptop shelf supports up to 11 lb.

Applications

- Easily switch between portrait and landscape modes to better accommodate your content or match the orientation of a source device
- Adjust the angle of a digital whiteboard or interactive display for a more comfortable writing angle during a brainstorming session
- Move a flat-panel display into a lobby, hallway or trade show booth to create temporary digital signage

System Requirements

- Flat-screen television, monitor, digital whiteboard or interactive display from 37 to 70 in.

Package Includes

- Base



- (4) Locking casters
- (2) Base columns
- (2) Upper columns
- (1) Equipment shelf
- (2) Shelf mounting brackets
- Front and rear covers
- Mounting plate
- (4) VESA extension adapter arms
- (4) Cable covers
- (5) Cable clips and holders
- (2) Wrenches
- Hex key, 4 mm
- Hex key, 5 mm
- (4) Washers
- (16) Spacers
- Assembly and mounting screws
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332257840
Device Compatibility	Monitor/HDTV; Projector
PHYSICAL	
Color	Black
Degrees of Motion	360° Rotate
Material of Construction	steel
Maximum Screen Size (cm)	177.8
Maximum Screen Size (in.)	70
Maximum Weight Capacity (kg)	70
Maximum Weight Capacity (lbs.)	154
Minimum Screen Size (cm)	93.87
Minimum Screen Size (in.)	37
Motion	Full



Mounting Location	Floor
Number of Displays	1
Shipping Dimensions (hwd / cm)	13.46 x 86.61 x 102.11
Shipping Dimensions (hwd / in.)	5.30 x 34.10 x 40.20
Shipping Weight (kg)	27.67
Shipping Weight (lbs.)	61.00
Unit Dimensions (hwd / in.)	64.2 x 36.2 x 27.6
Unit Weight (kg)	24.81
Unit Weight (lbs.)	54.7
VESA Pattern (mm)	200x200; 300x300; 350x350; 400x200; 400x400; 600x200; 600x400
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
SPECIAL FEATURES	
Cord Management	No
Security Lock	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>