

Rolling TV/Monitor Cart for 37" to 70" Flat-Screen Displays, Rotating Portrait/Landscape Mount

MODEL NUMBER: DMCS3770ROT



Heavy-duty mobile TV/monitor stand with rotatable mount allows one-touch transitions between portrait and landscape modes.

Features

Height Adjustable Display Stand Rolls from Room to Room Mobile mount for flat panel TVs, monitors and other displays, including Samsung Flip, Surface Hub2S and more Recommended for classrooms, lecture halls, offices, auditoriums and conference rooms Fits most displays from 37 to 70 in.

Flexible Features That Meet Your Specifications 5 degree tilt provides an ergonomic, more natural writing position Easily rotates for viewing in portrait or landscape modes

Rolls on Sturdy Metal Casters 4 in. swivel casters move smoothly through doorways and over thresholds All casters lock to hold stand securely in position while at rest

Durable Construction Made from steel Lower shelf holds A/V components, such as Blu-ray player Supports up to 154 lbs (69.9 kgs) Laptop shelf holds up to 11 lbs (4.9 kgs)

VESA Compliance Supports the following VESA mounting hole patterns: 200 x 200, 300 x 300, 350 x 350, 400 x 200, 400 x 400, 600 x 200 and 600 x 400

Highlights

- Supports most flat-panel monitors and interactive displays from 37 to 70 in. including Samsung Flip, Surface Hub2S and more.
- Mount rotates 90° with a single touch for portrait or landscape viewing; no tools needed
- Heavy-duty casters enable smooth rolling and lock to secure the cart at rest
- +5° tilt offers an ergonomic angle for writing on a whiteboard or interactive display
- Supports screens up to 154 lbs (69.9 kgs) Laptop shelf supports up to 11 lbs (4.9 kgs)

Applications

- Easily switch between portrait and landscape modes to better accommodate your content or match the orientation of a source device
- Adjust the angle of a digital whiteboard or interactive display for a more comfortable writing angle during a brainstorming session
- Move a flat-panel display into a lobby, hallway or trade show booth to create temporary digital signage

System Requirements

- Flat-screen television, monitor, digital whiteboard or interactive display from 37 to 70 in.

Package Includes

- Base
- (4) Locking casters
- (2) Base columns
- (2) Upper columns
- (1) Equipment shelf
- (2) Shelf mounting brackets
- Front and rear covers
- Mounting plate
- (4) VESA extension adapter arms
- (4) Cable covers
- (5) Cable clips and holders
- (2) Wrenches



Powering Business Worldwide

TRIPP LITE
SERIES

- Hex key, 4 mm
- Hex key, 5 mm
- (4) Washers
- (16) Spacers
- Assembly and mounting screws
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332257840
Device Compatibility	Monitor/HDTV; Projector
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	200x200; 300x300; 350x350; 400x200; 400x400; 600x200; 600x400
Motion	Full
Mounting Location	Floor
Degrees of Motion	360° Rotate
Minimum Screen Size (in.)	37
Minimum Screen Size (cm)	93.87
Maximum Screen Size (in.)	70
Maximum Screen Size (cm)	177.8
Maximum Weight Capacity (lbs.)	154
Maximum Weight Capacity (kg)	70
Number of Displays	1
Shipping Dimensions (hwd / in.)	5.30 x 34.10 x 40.20
Shipping Dimensions (hwd / cm)	13.46 x 86.61 x 102.11
Shipping Weight (lbs.)	61.00
Shipping Weight (kg)	27.67
Unit Dimensions (hwd / in.)	64.200 x 36.200 x 27.600
Unit Weight (lbs.)	54.7
Unit Weight (kg)	24.81
Assembly Required	Yes
FEATURES & SPECIFICATIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
Built-in Cable Management	No
Pre-Installed Casters	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.