


## Heavy-Duty Streamline Portrait Mobile Cart for 45" to 60" Flat-Panel Displays

MODEL NUMBER: DMCSPP4560HDS



Secure digital signage stand delivers your message to a classroom, lobby, trade show or other location with heavy foot traffic.

### Features

#### Set Up Your Digital Signage Wherever Your Audience Is

This streamline mobile TV stand fits most flat-panel displays, whiteboards and interactive displays from 45 to 60 inches (114 to 152 centimeters) in portrait mode. It's easy to assemble with for convenient setup wherever foot traffic flows, such as classrooms, trade shows, lecture halls, offices, auditoriums, restaurants, bars and hotels. It's ideal for setting up a digital whiteboard or interactive display for a virtual meeting or brainstorming session or showing videos in a multipurpose area where a permanent display is not feasible.

#### Heavy-Duty Frame Designed to Last

The aluminum and steel frame withstands the stress of repeated adjustments and supports up to 220 pounds (100 kilograms). Leveling feet at the bottom let you adapt your display to uneven floors. Heavy-duty locking casters are also included for rolling your display from one room to the next.

#### Includes Combo Lock to Keep Your Display Secure

The DMCSPP4560HDS features an anti-theft locking hole complete with a four-position combination lock to protect your display in heavy traffic areas.

#### Conveniently Manage Cables

Equipment cables route through clips on the stand's legs to keep them organized and avoid excessive clutter.

#### VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400 and 600 x 400. All hardware is included.

### Highlights

- Supports most monitors, whiteboards and interactive displays from 45 to 60 in.
- Durable aluminum and steel frame blends into any decor and supports up to 220 lb.
- Anti-theft locking hole with included 4-position combination lock keeps display secure
- Heavy-duty locking casters allow easy movement through doorways and into rooms
- Cable management clips keep cords organized and prevent cable clutter

### Package Includes

- DMCSPP4560HDS Streamline Portrait Mobile Cart
- Assembly hardware
- Owner's manual

## Specifications

### OVERVIEW



Powering Business Worldwide

TRIPP LITE  
SERIES

UPC Code	037332271983
Device Compatibility	Monitor/HDTV
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Aluminum, Steel
VESA Pattern (mm)	200x200; 300x200; 300x300; 400x200; 400x300; 400x400; 600x400
Motion	Fixed
Mounting Location	Floor
Minimum Screen Size (in.)	45
Minimum Screen Size (cm)	114.3
Maximum Screen Size (in.)	60
Maximum Screen Size (cm)	152.40
Maximum Weight Capacity (lbs.)	220
Maximum Weight Capacity (kg)	100
Number of Displays	1
Unit Dimensions (hwd / in.)	67.560 x 26.500 x 21.800
Unit Dimensions (hwd / cm)	171.60 x 67.31 x 55.37
Unit Weight (lbs.)	31.1
Unit Weight (kg)	14.11
Assembly Required	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Security Lock	Yes
Built-in Cable Management	No
Leveling Feet	Yes
Pre-Installed Casters	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.