

## Mobile Dual-Screen Video Wall - For Two 45" to 55" TVs and Monitors, Heavy Duty

MODEL NUMBER: DMCVW4555X2



Dual-screen mobile cart supports mounting of two flat-panel televisions or monitors to create a portable video wall.

### Features

#### Create a Mobile Video Wall with Two Flat-Panel Displays

The DMCVW4555X2 provides a convenient way to create a dual-screen video wall for a presentation or temporary digital signage and bring it to audiences in classrooms, lecture halls, offices, auditoriums, conference rooms and other locations where video resources are shared. Made primarily of steel and aluminum, this rolling video wall accommodates most flat-panel televisions or monitors from 45 to 55 inches that weigh up to 132 lb.

#### Effectively Share a Dual-Screen Video Wall

Four sturdy swivel casters provide smooth rolling through doorways and over thresholds, making it possible to share dual screens within a facility instead of purchasing multiple setups. When not in use, the cart can be rolled into a secure area for storage. Two of the casters lock to keep the cart in position while at rest. Cable management openings in the main column allow you to route power and audio/video cords, reducing clutter for a clean, professional look.

#### Easily Mount 45" to 55" Displays and Deter Theft

For hassle-free display compatibility, this rolling video wall supports the following VESA mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300 and 600 x 400. Fine adjustments can be made to the position of the displays using a hex key (included). The height of both mounting plates is adjustable, and the top display can be raised up to 67.7 inches above the floor. Three-position combination locks (included) secure the brackets to deter theft of the displays.

### Highlights

- Accommodates most flat-panel displays from 45 to 55 in.
- Display height adjusts up to 67.7 in. (top display)
- Combination locks secure brackets to help deter theft of displays
- Large swivel casters roll smoothly over carpet
- Supports up to 132 lb. per display

### Applications

- View video in a multipurpose area where a permanent installation is not practical
- Move a video wall into a meeting room for a presentation
- Advertise a special event without permanently mounting screens
- Roll a temporary digital signage installation into an auditorium
- Easily move a video wall to a secure area for storage between events

### Package Includes

- All DMCVW4555X2 components (assembly required)
- Assembly fasteners
- Display mounting fasteners
- (2) Three-position combination locks
- Hex keys
- Wrench
- Owner's manual



## Specifications

OVERVIEW	
UPC Code	037332239419
PHYSICAL	
Color	Black; Silver
Material of Construction	steel
Maximum Weight Capacity (kg)	60
Maximum Weight Capacity (lbs.)	132
Motion	Fixed
Mounting Location	Floor
Number of Displays	2
Shipping Dimensions (hwd / cm)	185.42 x 49.02 x 22.61
Shipping Dimensions (hwd / in.)	73.00 x 19.30 x 8.90
Shipping Weight (kg)	38.51
Shipping Weight (lbs.)	84.90
Unit Dimensions (hwd / cm)	171.96 x 83.57 x 70.10
Unit Dimensions (hwd / in.)	67.7 x 32.9 x 27.6
Unit Weight (kg)	31.48
Unit Weight (lbs.)	69.4
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	Yes
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>