Mobile Dual-Screen Video Wall - For Two 45" to 55" TVs and Monitors, Heavy Duty

MODEL NUMBER: **DMCVW4555X2**



Dual-screen mobile cart supports mounting of two flat-panel televisions or monitors to create a portable video wall.

Features

Create a Mobile Video Wall with Two Flat-Panel Displays The DMCVW4555X2 provides a convenient way to create a dual-screen video wall for a presentation or temporary digital signage and bring it to audiences in classrooms, lecture halls, offices, auditoriums, conference rooms and other locations where video resources are shared. Made primarily of steel and aluminum, this rolling video wall accommodates most flat-panel televisions or monitors from 45 to 55 inches that weigh up to 132 lbs (59.9 kgs)

Effectively Share a Dual-Screen Video Wall Four sturdy swivel casters provide smooth rolling through doorways and over thresholds, making it possible to share dual screens within a facility instead of purchasing multiple setups. When not in use, the cart can be rolled into a secure area for storage. Two of the casters lock to keep the cart in position while at rest. Cable management openings in the main column allow you to route power and audio/video cords, reducing clutter for a clean, professional look.

Easily Mount 45" to 55" Displays and Deter Theft For hassle-free display compatibility, this rolling video wall supports the following VESA mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300 and 600 x 400. Fine adjustments can be made to the position of the displays using a hex key (included). The height of both mounting plates is adjustable, and the top display can be raised up to 67.7 inches above the floor. Three-position combination locks (included) secure the brackets to deter theft of the displays.

Highlights

- Accommodates most flat-panel displays from 45 to 55 in.
- Display height adjusts up to 67.7 in. (top display)
- Combination locks secure brackets to help deter theft of displays
- Large swivel casters roll smoothly over carpet
- Supports up to 132 lbs (59.9 kgs) per display

Applications

- View video in a multipurpose area where a permanent installation is not practical
- Move a video wall into a meeting room for a presentation
- Advertise a special event without permanently mounting screens
- Roll a temporary digital signage installation into an auditorium
- Easily move a video wall to a secure area for storage between events

Package Includes

- All DMCVW4555X2 components (assembly required)
- Assembly fasteners
- Display mounting fasteners
- (2) Three-position combination locks
- Hex keys
- Wrench
- Owner’s manual

Specifications

OVERVIEW	
UPC Code	037332239419
Device Compatibility	Monitor/HDTV; Projector
PHYSICAL	
Color	Black; Silver

Material of Construction	steel
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400
Motion	Fixed
Mounting Location	Floor
Maximum Weight Capacity (lbs.)	132
Maximum Weight Capacity (kg)	60
Number of Displays	2
Shipping Dimensions (hwd / in.)	8.90 x 19.30 x 73.00
Shipping Dimensions (hwd / cm)	22.61 x 49.02 x 185.42
Shipping Weight (lbs.)	84.90
Shipping Weight (kg)	38.51
Unit Dimensions (hwd / in.)	67.700 x 32.900 x 27.600
Unit Dimensions (hwd / cm)	171.96 x 83.57 x 70.10
Unit Weight (lbs.)	69.4
Unit Weight (kg)	31.48
FEATURES & SPECIFICATIONS	
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.