

## Dual-Extension Monitor Mount for Slat Wall System, 13" to 32" Displays, TAA

MODEL NUMBER: DMSW1332LTAA



Mounts your 13 to 32 in. television or monitor on a slat wall surface to provide optimal viewing angles.

### Features

#### Positions Your Monitor at the Perfect Viewing Angle

This VESA-compliant TV wall mount lets you place your digital signage, monitor or television where everyone can see it best. It's ideal for office, hybrid and work-from-home environments, including office cubicles, art tables and lab workbenches. The stylish aluminum mount fits most flat-panel displays from 13 to 32 inches and supports up to 22 pounds (10 kg).

#### Swivel and Tilt the Screen to Find the Perfect and Most Comfortable Viewing Angle

The articulating arm adjusts independently to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features  $-15^{\circ}$  to  $+15^{\circ}$  tilt,  $-90^{\circ}$  to  $+90^{\circ}$  swivel and full  $360^{\circ}$  rotation for positioning your screen just right. The arm extends up to 16 inches from the slat.

#### VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this slat wall mount supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100.

#### Requires Slat Wall System for Installation

The DMSW1332LTAA easily attaches to the Slat Rail with Posts (DMSWKITTAA) or the Slat Rail (DMSWSLATTAA), both sold separately. Your monitor is elevated above the desktop, which frees up precious workspace. You can also slide the monitor along grooves and then adjust the viewing angle for optimal ergonomics. Grooves on both sides of the slat rail accommodate independently adjustable monitor setups when desks are pushed together back-to-back. Two other monitor mounts (DMSW1332MTAA and DMSW1332STAA, sold separately) are also available.

#### TAA-Compliant for GSA Schedule Purchases

The DMSW1332LTAA is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

## Specifications

### Highlights

- TV mount for slat walls adjusts viewing angle easily with just a single touch
- $-15^{\circ}$  to  $+15^{\circ}$  tilt,  $-90^{\circ}$  to  $+90^{\circ}$  swivel and  $360^{\circ}$  rotation help you find the perfect angle
- Stylish aluminum construction blends into any decor and supports up to 22 lb.
- Requires installation of Slat Rail with Posts (DMSWKITTAA, sold separately)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

- Displays from 13 in. to 32 in. and up to 22 lb. with a VESA mounting hole pattern of 75 x 75 or 100 x 100
- Works with DMSWKITTAA Slat Rail with Posts and DMSWSLATTAA Slat Rail

### Package Includes

- DMSW1332LTAA Monitor Mount
- (4) M4 x 10 screws
- Hex wrench
- (2) Cable management clips
- Owner's Manual



Powering Business Worldwide

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332286499
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
VESA Pattern (mm)	75x75; 100x100
Motion	Full Motion/Rotate; Swivel; Tilt
Mounting Location	Desktop
Degrees of Motion	360 degree swivel, 60 degree tilt
Minimum Screen Size (in.)	13
Maximum Screen Size (in.)	32
Maximum Weight Capacity (lbs.)	22
Maximum Weight Capacity (kg)	10
Min/Max Arm Extension (in.)	18.6
Number of Displays	1
Shipping Dimensions (hwd / in.)	20.50 x 4.90 x 4.70
Shipping Dimensions (hwd / cm)	52.07 x 12.45 x 11.94
Shipping Weight (lbs.)	5.80
Shipping Weight (kg)	2.63
Unit Dimensions (hwd / in.)	18.600 x 3.900 x 3.800
Unit Dimensions (hwd / cm)	16.2 x 9.9 x 9.65
Unit Weight (lbs.)	3.6
Unit Weight (kg)	1.63
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
Height Adjustable	Yes
Locking	No
Pre-Installed Casters	No
Outdoor Use	No



Powering Business Worldwide

TRIPP LITE  
SERIES

STANDARDS & COMPLIANCE	
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.