

Interactive Flat-Panel Touchscreen Display, 4K @ 60 Hz, UHD, 55 in.

MODEL NUMBER: DMTP55NO



55 in. 4K interactive touchscreen with Android OS allows remote team collaboration with screen sharing and low-latency response.

Features

An Advanced Presentation Platform Perfect for Group Brainstorming Sessions

Tripp Lite's Interactive Flat-Panel Touchscreen Display encourages and assists group collaboration and audience participation – a crucial tool as organizations implement work-from-home strategies for employee safety and operational continuity. This best-in-class 55-inch 4K display includes an embedded Android operating system, providing a flexible presentation platform compatible with a wide array of apps and devices.

Take Information Directly to Your Audience Anywhere

The DMTP55NO helps you promote collaboration, enable interactive presentations and facilitate communication between local and remote teams. It's ideal for classrooms, libraries, conference rooms, meeting rooms and other office environments in education, corporate, healthcare, hospitality, retail, government, defense and public safety settings. The VESA-compatible display mounts easily to a wall mount or mobile cart (each sold separately) for shared workflow in any location.

Designed for Dynamic Interactivity That Lets Everyone Be Part of the Team

The display's remote collaboration capability is ideal to keep teams working together, wherever members may be. Built-in wireless networking, remote screen sharing, and a wide range of pre-installed tools aid problem-solving and free expression of ideas. In addition, a detachable high-definition webcam beams the entire meeting area straight to off-site collaborators and partners, allowing anyone to participate in meetings, presentations and group discussions from outside the office. A built-in 40-watt speaker system ensures everyone in the room will hear every idea clearly.

All the World's Information Available, Literally, at Your Fingertips

The 55-inch 4K display boasts patented touchscreen technology with low-latency response and 20 points of multi-touch. Use your fingers or the included battery-free stylus to write notes, check email, create presentations, stream 4K video and surf the web. The large touchscreen monitor is built for ultra-fast, ultra-precise interactivity for multiple concurrent users. It all makes for an immersive and expansive experience that basic electronic whiteboards can't match.

Specifications

Highlights

- Razor-sharp 55 in. 4K touchscreen monitor ideal for interactive presentations
- Android presentation platform compatible with wide range of apps and hardware
- Detachable HD webcam captures entire meeting area for sharing anywhere
- Remote screen sharing allows anyone to participate, whether in office or at home
- Promotes collaborative teamwork while work-from-home strategies are in place

Applications

- Brainstorm ideas and collaborate on a group project in a conference room or huddle space
- Show math problems, outline lessons and organize information to students in a classroom or library
- Describe problem-solving job solutions in a warehouse or other industrial setting
- Present remodeling ideas and other home building concepts to potential real estate clients
- Give video or multimedia presentations at a school assembly, trade show or sales meeting

Package Includes

- 55 in. interactive flat-panel touchscreen display
- Detachable HD webcam
- (2) Stylus pens with replacement tips
- (4) Wi-fi antennas
- Remote control
- (2) AAA batteries
- Owner's manual

OVERVIEW	
UPC Code	037332257918
Product Type	Interactive Touchscreen
Device Compatibility	Monitor/HDTV
VIDEO	
Max Supported Video Resolution	4K @ 60 Hz
DISPLAY	
Screen Size	55
Touch Technology	Ultra Slim IR (13mm depth)
Number of Touch Points (Android)	10
Response Time	<8 ms (1 touch)
Aspect Ratio	16:9
Viewing Angle	178/178 degrees
Brightness	350 cd/m2
Contrast Ratio	1300:1
Tilt	+5 to -10 degrees
Camera	Detachable HD webcam (1080p); Supports video calling
Audio	Soundbar speakers (20W x 2) with subwoofer
Accessories (Included)	2 stylus pens with replacement tips; remote control
Remote User Interface (RUI)	Power LED, battery charge level LEDs, on/off button, alarm mute button
Other Features	Anti-glare 4mm tempered glass
COMPUTE	
Processor Type	Intel® Core™ i7 6500U
Processor Speed	4.20 GHz
Maximum Memory	Upgradable to 32GB
Storage	128GB Solid State Drive (SSD)
Pre-Installed Operating Systems	Android 6
Graphics Card	Intel® UHD Graphics 500 Series
POWER	
Input Voltage(s)	120V or 230V
Power Cord Length (ft.)	6
CONNECTIONS	



Powering Business Worldwide



Input Ports	Front: HDMI; USB 2.0; USB for touch Rear: (4) HDMI; DisplayPort; VGA; USB for camera; (3) USB 2.0 (Android only); (2) USB for touch; (3) 3.5 mm audio
Output Ports	Rear: (2) HDMI; (2) 3.5 mm Audio
Ethernet Interface	(RS232 (D-sub 9-Pin), LAN(RJ45))
Serial Interface	RS-232 (DB9)
PHYSICAL	
Color	Black; Silver
VESA Pattern (mm)	400x300
Shipping Dimensions (hwd / in.)	8.70 x 37.10 x 55.10
Shipping Weight (kg)	43.00
Unit Dimensions (hwd / in.)	32.300 x 50.400 x 3.600
Unit Dimensions (hwd / cm)	82 x 128 x 9.1
Unit Weight (lbs.)	119.1
Unit Weight (kg)	54.02
FEATURES & SPECIFICATIONS	
Cord Management	No
Security Lock	No
Built-in Cable Management	Yes
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 60950-1 (Canada); UL 60950-1
Product Compliance	RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.