

Interactive Flat-Panel Touchscreen Display with PC, 4K @ 60 Hz, UHD, 65 in.

MODEL NUMBER: DMTP65OPS



65 in. 4K interactive touchscreen with Windows 10 PC and Android OS allows remote team collaboration with screen sharing and low-latency response.

Features

An Advanced Presentation Platform Perfect for Group Brainstorming Sessions

Tripp Lite's Interactive Flat-Panel Touchscreen Display encourages and assists group collaboration and audience participation – a crucial tool as organizations implement work-from-home strategies for employee safety and operational continuity. This best-in-class 65-inch 4K display includes both an embedded Android operating system and a full-featured touch-enabled Windows 10 PC, providing a flexible presentation platform compatible with a wide array of apps and hardware, not just for Android and Windows, but also Chrome, iOS and Mac OS devices.

Take Information Directly to Your Audience Anywhere

The DMTP65OPS helps you promote collaboration, enable interactive presentations and facilitate communication between local and remote teams. It's ideal for classrooms, libraries, conference rooms, meeting rooms and other office environments in education, corporate, healthcare, hospitality, retail, government, defense and public safety settings. The VESA-compatible display mounts easily to a wall mount or mobile cart (each sold separately) for shared workflow in any location.

Designed for Dynamic Interactivity That Lets Everyone Be Part of the Team

The display's remote collaboration capability is ideal to keep teams working together, wherever members may be. Built-in wireless networking, remote screen sharing, and a wide range of pre-installed tools aid problem-solving and free expression of ideas. In addition, a detachable high-definition webcam beams the entire meeting area straight to off-site collaborators and partners, allowing anyone to participate in meetings, presentations and group discussions from outside the office. A built-in 40-watt speaker system ensures everyone in the room will hear every idea clearly.

All the World's Information Available, Literally, at Your Fingertips

The 65-inch 4K display boasts patented touchscreen technology with low-latency response and 20 points of multi-touch. Use your fingers or the included battery-free stylus to write notes, check email, create presentations, stream 4K video and surf the web. Share resources with your fellow team members, edit documents in real time and save everything in the cloud. The large touchscreen monitor is built for ultra-fast, ultra-precise interactivity for multiple concurrent users. It all makes for an immersive and expansive experience that basic electronic whiteboards can't match.

Highlights

- Razor-sharp 65 in. 4K touchscreen display ideal for interactive presentations
- Windows 10 PC with Android compatible with wide array of apps and hardware
- Detachable HD webcam captures entire meeting area for sharing anywhere
- Remote screen sharing allows anyone to participate, whether in office or at home
- Promotes collaborative teamwork while work-from-home strategies are in place

Applications

- Brainstorm ideas and collaborate on a group project in a conference room or huddle space
- Show math problems, outline lessons and organize information to students in a classroom or library
- Describe problem-solving job solutions in a warehouse or other industrial setting
- Present remodeling ideas and other home building concepts to potential real estate clients
- Give video or multimedia presentations at a school assembly, trade show or sales meeting

Package Includes

- 65 in. interactive flat-panel



touchscreen display with built-in PC

- Detachable HD webcam
- (2) Stylus pens with replacement tips
- (4) Wi-fi antennas, large
- (2) Wi-fi antennas, small
- Remote control
- (2) AAA batteries
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332257901
Product Type	Interactive Touchscreen
Device Compatibility	Monitor/HDTV
VIDEO	
Maximum Resolution	3840 x 2160 (4K) @ 60 Hz
DISPLAY	
Screen Size	65
Touch Technology	Ultra Slim IR (13mm depth)
Number of Touch Points	20
Response Time	<8 ms (1 touch)
Aspect Ratio	16:9
Viewing Angle	178/178 degrees
Brightness	350 cd/m2
Contrast Ratio	1300:1
Tilt	+5 to -10 degrees
Camera	Detachable HD webcam (1080p); Supports video calling
Audio	Soundbar speakers (20W x 2) with subwoofer
Accessories (Included)	2 stylus pens with replacement tips; remote control
Remote User Interface (RUI)	Power LED, battery charge level LEDs, on/off button, alarm mute button
Other Features	Anti-glare 4mm tempered glass



COMPUTE	
Processor Type	Intel® Core™ i7 6500U
Processor Speed	4.20 GHz
Installed Memory	4GB Dual Channel DDR4 2133Mhz
Maximum Memory	Upgradable to 32GB
Storage	128GB Solid State Drive (SSD)
Pre-Installed Operating Systems	Android 6; Windows 10 Pro, 64 Bit (also Windows 7 & 8; Mac 10.10 and 10.14)
Graphics Card	Intel® UHD Graphics 500 Series
POWER	
Input Voltage(s)	120V
Power Cord Length (ft.)	6
PHYSICAL	
Color	Black; Silver
Unit Dimensions (hwd / cm)	93.2 x 149.1 x 9.14
Unit Dimensions (hwd / in.)	36.7 x 58.7 x 3.6
Unit Weight (kg)	54.02
Unit Weight (lbs.)	119.1
CONNECTIONS	
Input Ports	Front: HDMI; USB 2.0; USB for touch Rear: (3) HDMI; DisplayPort; VGA; USB for camera; (3) USB 2.0 (Android only); (2) USB 2.0; (2) USB 3.0; (2) USB for touch; (3) 3.5 mm audio
Output Ports	Rear: (2) HDMI; (2) 3.5 mm Audio
Ethernet Interface	(2) RJ45 (100 Mbps)
Serial Interface	RS-232 (DB9)
Wireless Interface	WiFi 5 (IEEE 802.11ac, 4 large antennas, 2 small antennas); Bluetooth 4.0
SPECIAL FEATURES	
Security Lock	No
Built-in Cable Management	Yes
Pre-installed Casters	Yes
STANDARDS & COMPLIANCE	
United States	Display: UL60950-1:2007 (2nd Ed)+A1+A2 R10.14
Canada	Display: CAN/CSA-C22.2 No. 60950-1:2007 (2nd Ed) +A1:2011 +A2:2014
International	Display: IEC60950-1:2005 (2nd Ed)+A1:2009+A2:2013



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Compliance	Display: Class A; EN55032:2012+AC:2013; EN55035:2017 FCC/ICES: Display: CLASS A; 47 CFR FCC PART 15 SUBPART B; 47 CFR FCC PART 15 SUBPART CEMI/EMC Standards: Class A; EN55032:2012+AC:2013; EN55035:2017
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>