


Swivel/Tilt Corner Wall Mount for 37" to 70" TVs and Monitors - Flat/Curved

MODEL NUMBER: DMWC3770M



Wall mount with split wall plates supports installation of a flat-panel or curved-screen television or monitor in a corner.

Features

Corner Mount Your Flat-Panel or Curved-Screen TV or Monitor Split wall plates allow the DMWC3770M to mount on both walls of a corner, providing a wide viewing angle in home theaters, classrooms, boardrooms, hotels, bars and restaurants. It's also a great display solution for rooms with limited wall space due to window placement or furniture arrangements. This true corner mount accommodates most flat-panel or curved-screen televisions or monitors from 37 to 70 inches. Maximum weight supported is 99 lbs (44.9 kgs)

Adjust the Display Angle for Comfortable Viewing One-touch adjustment capability makes it easy to optimize viewing angles. For maximum screen visibility, the articulating arms can swivel 90° left or right. The -8° to +5° tilt and -5° to +5° screen level adjustment help minimize glare and improve the audience's viewing experience.

Rely on Durable All-Metal Construction with Convenient Cable Access Made of steel with a black powder-coated finish, this full-motion wall mount withstands the stress of repeated adjustments and use in public areas. An open frame design supports easy access to cables.

VESA Compliance Ensures Display Compatibility VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards, such as universal mounting hole patterns, for TVs and monitors. For hassle-free display compatibility, this corner wall mount supports the following VESA mounting hole patterns: 100 x 100, 200 x 100, 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300 and 600 x 400. Mounting hardware is included.

Specifications

OVERVIEW	
UPC Code	037332240538
Device Compatibility	Monitor/HDTV

Highlights

- Accommodates most flat or curved screens from 37 to 70 in.
- Split wall plates mount on the adjacent walls of a corner
- One-touch adjustment makes it easy to change the viewing angle
- 90° swivel, -8° to +5° tilt and -5° to +5° screen adjustment maximize viewing comfort
- Supports displays up to 99 lbs (44.9 kgs)

Applications

- Provide flexible viewing options for seating areas in home theaters
- Take advantage of unused wall space in a classroom or conference room
- Optimize viewing for more patrons in a bar or restaurant
- Mount displays in a hotel lobby without interfering with wall art

Package Includes

- DMWC3770M corner wall mount
- Mounting fasteners
- Wrench
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 200x100; 200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400
Motion	Full
Mounting Location	Wall
Degrees of Motion	90 Swivel -8/+5 Level Adjustment
Minimum Screen Size (in.)	37
Maximum Screen Size (in.)	70
Maximum Weight Capacity (lbs.)	99
Maximum Weight Capacity (kg)	45
Min/Max Arm Extension (in.)	4.92 min to 20.27 max
Min/Max Arm Extension (cm)	Hasta 62 cm [24.4"] de la pared
Number of Displays	1
Shipping Dimensions (hwd / in.)	31.20 x 12.70 x 3.30
Shipping Dimensions (hwd / cm)	79.25 x 32.26 x 8.38
Shipping Weight (lbs.)	16.80
Shipping Weight (kg)	7.62
Unit Dimensions (hwd / in.)	24.400 x 25.300 x 16.500
Unit Dimensions (hwd / cm)	61.98 x 64.26 x 41.91
Unit Weight (lbs.)	13.9
Unit Weight (kg)	6.30
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.