

Fixed Wall Mount for 26" to 55" TVs and Monitors

MODEL NUMBER: DWF2655X



Low-profile mount hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants.

Description

The VESA-compliant DWF2655X Fixed Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 26 to 55 inches. The low-profile mount is concealed behind the display to give a sleek, professional appearance. Frame is open for easy wall access. Mounting rails adjust horizontally to compensate for off-center wall studs. Built-in bubble level allows accurate display leveling. Durable all-metal frame with scratch-resistant powder-coated finish supports up to 165 pounds. Mounting hardware included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm and 400 x 400 mm

Features

Mounts Your TV or Monitor to the Wall

- Fits most flat-panel televisions, monitors and other displays from 26 to 55 in.
- Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants
- Mounts out of sight behind display for sleek, professional appearance
- Mounting hardware included

Durable Metal Construction

- Supports up to 165 lb.
- Open frame allows easy wall access
- Adjustable mounting rails compensate for off-center wall studs
- Built-in bubble level for accurate display leveling
- Scratch-resistant powder-coated finish

VESA Compliance

- Supports the following VESA mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200

Highlights

- Fits most flat-panel displays from 26 to 55 in.
- Hangs out of sight for a sleek, professional appearance
- Adjustable mounting rails compensate for off-center wall studs
- Supports up to 165 lb.

Package Includes

- DWF2655X Fixed Wall Mount for 26" to 55" TVs and Monitors
- (4) M5 x 10 screws
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- (4) Anchor bolts
- (4) Concrete anchors
- (4) D6 washers
- Owner's manual



mm, 400 x 300 mm and 400 x 400 mm

Specifications

OVERVIEW	
UPC Code	037332183491
PHYSICAL	
Color	Black
Degrees of Motion	Fixed
Material of Construction	Steel
Maximum Screen Size (cm)	139.7
Maximum Screen Size (in.)	55
Maximum Weight Capacity (kg)	75
Maximum Weight Capacity (lbs.)	165
Min/Max Arm Extension (cm)	N/A
Min/Max Arm Extension (in.)	N/A
Minimum Screen Size (cm)	66.04
Minimum Screen Size (in.)	26
Motion	Fixed
Mounting Location	Wall
Number of Displays	1
Shipping Dimensions (hwd / cm)	5.08 x 12.19 x 49.02
Shipping Dimensions (hwd / in.)	2.00 x 4.80 x 19.30
Shipping Weight (kg)	1.91
Shipping Weight (lbs.)	4.20
Unit Dimensions (hwd / cm)	23.01 x 46.41 x 2.99
Unit Dimensions (hwd / in.)	9.06 x 18.27 x 1.18
Unit Weight (kg)	2.05
Unit Weight (lbs.)	4.51
VESA Pattern (mm)	100x100; 100x200; 200x100; 200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cord Management	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>