

Fixed TV Wall Mount 32-55", Heavy Duty, Security, Televisions & Monitors - Flat/Curved, UL Certified

MODEL NUMBER: DWFSC3255MUL



Security wall mount with combination lock mounts your flat-panel or curved-screen television or monitor to the wall.

Features

Security Wall Mount Hangs Your Flat-Panel or Curved-Screen TV or Monitor on the Wall

Ideal for home theaters, classrooms, conference rooms, hotels, bars, restaurants or anywhere else you may want to show off a television or monitor, this heavy-duty TV wall mount is hidden out of sight behind the display for a sleek, professional appearance. It fits most flat-panel or curved-screen displays from 32 to 55 inches and up to 99 pounds. Mounting hardware is included.

Durable All-Metal Construction Provides Convenient Cable Access

The monitor wall mount is constructed from heavy-duty steel with a powder-coated black finish that resists scratches. Rear openings with smooth edges enable easy access to cables. A built-in bubble level helps ensure your display is evenly mounted. This heavy-duty wall mount is function- and weight-tested to 150 pounds in accordance with UL Standard 2442.

Designed to Keep Your Display Safe and Secure

This security wall mount was conceived with your television or monitor's safety in mind, especially if the display is located in a public area with unguarded traffic, such as a library, classroom or hotel lobby. It comes with a solid steel security bar that slides through the mounting brackets and is secured into place with an included three-position combination lock.

Complies with VESA Standards

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing industry-wide standards for products like flat-panel TVs and monitors. To comply with these standards, most manufacturers use a series of universal mounting hole patterns, measured in millimeters, on the backs of the products. Measure the vertical and horizontal distances between the holes on the back of your display or refer to your display's owner's manual to find its VESA pattern. This fixed TV wall mount conforms to VESA-compliant displays with any of the following standard mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300 and 400 x 400.

5-Year Warranty

The DWFSC3255MUL is backed by a 5-year warranty, ensuring reliability and performance.

Highlights

- Accepts most popular flat- or curved-screen displays from 32 to 55 in. and up to 99 lb.
- Function- and weight-tested in accordance with UL Standard 2442 up to 150 lb.
- Solid steel security bar and included combo lock deters tampering and theft
- Open architecture and built-in level enable easy cable access and accurate leveling
- Complies with VESA standards to ensure compatibility with your display

Applications

- Mount a flat- or curved-screen monitor or TV in a conference room, restaurant, bar, lobby or anywhere else digital signage is needed
- Secure an expensive display in a hotel lobby, classroom, library, hospital, truck stop or other public area with unguarded foot traffic

Package Includes

- Wall plate
- (2) Adapter brackets
- Security bar
- (2) End caps
- (4) End cap screws
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws



- (4) M8 x 50 screws
- (4) Washers
- (8) Small spacers
- (8) Large spacers
- (4) Anchor bolts
- (4) Concrete anchors
- (4) 20 mm washers
- Combination lock
- Hex key
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332213716
PHYSICAL	
Color	Black
Degrees of Motion	Fixed
Material of Construction	Steel
Maximum Screen Size (cm)	139.7
Maximum Screen Size (in.)	55
Maximum Weight Capacity (kg)	68
Maximum Weight Capacity (lbs.)	150
Minimum Screen Size (cm)	81.28
Minimum Screen Size (in.)	32
Motion	Fixed
Mounting Location	Wall
Number of Displays	1
Shipping Dimensions (hwd / cm)	54.86 x 16.51 x 4.57
Shipping Dimensions (hwd / in.)	21.60 x 6.50 x 1.80
Shipping Weight (kg)	2.45
Shipping Weight (lbs.)	5.40
Unit Dimensions (hwd / cm)	51.5 x 44.0 x 2.6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (hwd / in.)	20.3x17.3 x 1.0
Unit Weight (kg)	1.83
Unit Weight (lbs.)	4.03
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
CERTIFICATIONS	
Certifications	UL
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>