

Full-Motion Wall-Mount with Screen Level Adjustment for 13" to 27" Flat-Screen Displays

MODEL NUMBER: DWM1323SP



Highlights

- SEE NEW MODEL - DWM1327SP
- Can be used to increase available desk/table space in office applications
- Fits most flat-panel displays from 13" to 27"
- Convenient one-touch display adjustment for easy view optimization
- Wide range of motion with -15° to +15° tilt, 180° swivel and -2° to +2° screen level adjustment capability
- Supports up to 33 lbs.
- 5-year warranty

Package Includes

- DWM1323SP full mption flat screen wall mount
- mounting hardware
- manual

Description

Tripp Lite's VESA-compliant DWM1323SP Full-Motion Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its sleek design features convenient one-touch display adjustment with tilt and swivel capabilities and fits most 13- to 27-inch flat-panel displays. Its durable, all-metal frame with soft, rubber feel finish withstands the stress of repeated use and blends easily into any décor. It comes with all necessary mounting hardware and supports weights of up to 33 lbs. For peace of mind, the DWM1323SP comes backed by a 5-year warranty.

Features

- Tripp Lite's VESA-compliant DWM1323SP Full-Motion Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation
- Sleek design features convenient one-touch display adjustment with tilt and swivel capabilities
- Fits most 13- to 27-inch flat-panel displays
- Durable, all-metal frame with soft, rubber feel finish withstands the stress of repeated use and blends easily into any décor
- Includes all necessary mounting hardware and supports weights of up to 33 lb
- 5-year warranty

Specifications

OVERVIEW	
UPC Code	037332178831
PHYSICAL	
Color	Black; Silver



Powering Business Worldwide



Material of Construction	Metal
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 180 Swivel; -2/+2 Level Adjustment
Maximum Weight Capacity (lbs.)	33
Maximum Weight Capacity (kg)	15
Shipping Dimensions (hwd / in.)	3.54 x 15.75 x 19.69
Shipping Dimensions (hwd / cm)	8.99 x 40.00 x 50.01
Shipping Weight (lbs.)	8.64
Shipping Weight (kg)	3.92
Unit Dimensions (hwd / in.)	7.480 x 5.200 x 22.830
Unit Weight (lbs.)	8.64
Unit Weight (kg)	3.92
FEATURES & SPECIFICATIONS	
Cord Management	No
Tools Necessary	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.