

## Swivel/Tilt Wall Mount with Screen Adjustment for 13" to 27" TVs and Monitors

MODEL NUMBER: DWM1327SP



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

### Description

The VESA-compliant DWM1327SP Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants, it fits most flat-panel displays from 13 to 27 inches.

The full-motion swivel arm can be independently adjusted for angle and height to give you maximum flexibility in positioning your display to fit your environment and comfort level. A 180° swivel, -15° to +15° tilt and -2° to +2° screen level adjustment capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with soft rubber-feel finish supports up to 33 lbs (14.9 kgs). Comes fully assembled for quick mounting to the wall with included hardware. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm and 100 x 100 mm.

### Features

**Mounts Your TV or Monitor to the Wall** Fits most flat-panel televisions, monitors and other displays from 13 to 27 in. Ideal for home, office, hotels, bars and restaurants Full-motion swivel arm adjusts independently for angle and height Mounting hardware included

**Convenient One-Touch Adjustment** 180° swivel, -15° to +15° tilt and -2° to +2° screen level adjustment capability provides comfortable viewing from multiple angles

**Durable Metal Construction** Supports up to 33 lbs (14.9 kgs) Soft rubber-feel finish with decorative covers blends with any décor Fully assembled for immediate installation Display cable attaches to mount to reduce clutter

**VESA Compliance** Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm

## Specifications

### OVERVIEW

### Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- 180° swivel, -15° to +15° tilt and -2° to +2° screen adjustment
- Supports up to 33 lbs (14.9 kgs)

### Package Includes

- DWM1327SP Swivel/Tilt Wall Mount for 13" to 27" TVs and Monitors
- (4) M4 screws
- (4) M5 screws
- (4) Washers
- (3) Anchor bolts
- (3) Concrete anchors
- Wrench
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual

UPC Code	037332183538
Device Compatibility	Monitor/HDTV
<b>PHYSICAL</b>	
Color	Black; Silver
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 180 Swivel; -2/+2 Level Adjustment
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	33
Maximum Weight Capacity (kg)	15
Min/Max Arm Extension (in.)	2.16 min to 22.85 max
Min/Max Arm Extension (cm)	5.49 min to 58.04 max
Number of Displays	1
Shipping Dimensions (hwd / in.)	3.54 x 15.75 x 19.69
Shipping Dimensions (hwd / cm)	8.99 x 40.00 x 50.01
Shipping Weight (lbs.)	8.64
Shipping Weight (kg)	3.92
Unit Dimensions (hwd / in.)	7.480 x 5.200 x 22.830
Unit Dimensions (hwd / cm)	19 x 47.5 x 13.2
Unit Weight (lbs.)	8.64
Unit Weight (kg)	3.92
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; RoHS3; REACH

**WARRANTY & SUPPORT**

Product Warranty Period  
(Worldwide)

5-year limited warranty