

Swivel/Tilt Wall Mount for 17" to 42" TVs and Monitors, 80° Swivel, -15° to +15° Tilt, -4° to +4° Screen Adjustment

MODEL NUMBER: DWM1742MN



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

Description

The VESA-compliant DWM1742MN Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 17 to 42 inches.

Adjust the display angle to fit your environment and comfort level. An 80° swivel, -15° to +15° tilt and -4° to +4° screen level adjustment capability minimizes glare and provides comfortable viewing from multiple angles.

- Durable all-metal frame with scratch-resistant powder-coated finish supports up to 115 lbs (52.2 kgs). Comes fully assembled for quick mounting to the wall with included hardware. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 75 x 200 mm, 100 x 100 mm, 200 x 100 mm and 200 x 200 mm

Features

Mounts Your TV or Monitor to the Wall Fits most flat-panel televisions, monitors and other displays from 17 to 42 in. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Display angle adjusts to fit your environment and comfort level. Mounting hardware included.

Convenient One-Touch Adjustment 80° swivel, -15° to +15° tilt and -4° to +4° screen level adjustment capability provides comfortable viewing from multiple angles.

Durable Metal Construction Supports up to 115 lbs (52.2 kgs). Scratch-resistant powder-coated finish. Fully assembled for immediate installation.

VESA Compliance Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 75 x 200 mm, 100 x 100 mm, 200 x 100 mm and 200 x 200 mm.

Specifications

OVERVIEW

Highlights

- Fits most flat-panel displays from 17 to 42 in.
- One-touch adjustment for comfortable viewing
- 80° swivel, -15° to +15° tilt and -4° to +4° screen adjustment
- Supports up to 115 lbs (52.2 kgs)

Package Includes

- DWM1742MN Swivel/Tilt Wall Mount for 17" to 42" TVs and Monitors
- (4) M4 x 14 screws
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M8 x 20 screws
- (4) D5 washers
- (4) D8 washers
- (8) Small spacers
- (3) Anchor bolts
- (3) Concrete anchors
- (3) D6 washers
- Hex key, 4 mm
- Owner's manual

UPC Code	037332183552
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 200x100; 200x200; 75x100; 75x200; 75x75
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 80 Swivel; -4/+4 Level Adjustment
Minimum Screen Size (in.)	17
Minimum Screen Size (cm)	43.18
Maximum Screen Size (in.)	42
Maximum Screen Size (cm)	106.68
Maximum Weight Capacity (lbs.)	115
Maximum Weight Capacity (kg)	52
Min/Max Arm Extension (in.)	1.30 min to 2.20 max
Min/Max Arm Extension (cm)	3.30 min to 5.89 max
Number of Displays	1
Shipping Dimensions (hwd / in.)	3.60 x 9.10 x 9.30
Shipping Dimensions (hwd / cm)	9.14 x 23.11 x 23.62
Shipping Weight (lbs.)	3.60
Shipping Weight (kg)	1.63
Unit Dimensions (hwd / in.)	7.870 x 2.200 x 1.280
Unit Dimensions (hwd / cm)	15.5 x 8.9 x 3.3
Unit Weight (lbs.)	3.63
Unit Weight (kg)	1.65
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

5-year limited warranty