

Full-Motion TV Wall Mount with Fully Articulating Arm for 23" to 55" Flat-Screen Displays

MODEL NUMBER: DWM2355S



Mounts your 23 to 55 in. television to the wall of your home theater, office, restaurant or boardroom to provide optimal viewing angles.

Features

Mounts Your TV or Monitor to the WallFits most flat-panel televisions, monitors and other displays from 23 to 55 in. Ideal for home theaters, offices, classrooms, boardrooms, hotels, bars and restaurants Full-motion articulating arm adjusts independently for angle and height Mounting hardware included Mounts on wood or concrete block

Convenient One-Touch Adjustment180° swivel and -15° to 15° tilt capability provides comfortable viewing from multiple angles

Durable Metal ConstructionSupports up to 51 lbs (23.1 kgs) Soft rubber-feel finish tolerates frequent handling and blends with any décor Display cables tuck inside articulating arm to prevent clutter

VESA ComplianceConforms with VESA-compliant universal mounting hole patterns

Highlights

- TV wall mount with articulating gas-spring arm adjusts easily with just a single touch
- -15° to +5° tilt and -90° to +90° swivel helps you find the perfect angle to avoid glare
- Durable steel construction blends into any décor and supports up to 51 lbs (23.1 kgs)
- Display cables attach to arm to reduce clutter and keep cords organized
- VESA compliance ensures compatibility with most popular mounting hole patterns

Applications

- Mounting a flat-screen television or monitor in an office lobby, conference room, bar, restaurant, airport or anywhere else digital signage is desired
- Installing a TV in your home theater that can be easily adjusted to accommodate the comfort levels of the audience

System Requirements

- Flat-screen television or monitor from 23 to 55 in.

Package Includes

- Wall plate with articulating arm
- VESA plate
- (4) VESA adapter brackets
- (2) Wall plate end caps
- (4) Nuts
- (4) Bolts
- Wrench
- Hex key, 4 mm
- Hex key, 6 mm
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (4) D5 washers
- (4) D8 washers
- (8) Small spacers

- (8) Large spacers
- (3) Anchor bolts
- (3) Concrete anchors
- (3) Washers
- Owner's manual

Specifications

| OVERVIEW | |
|---------------------------------|--|
| UPC Code | 037332258779 |
| Device Compatibility | Monitor/HDTV |
| PHYSICAL | |
| Color | Black |
| Material of Construction | Steel |
| VESA Pattern (mm) | 75x75; 100x100; 200x100; 200x200; 300x300; 400x200; 400x300; 400x400 |
| Motion | Full |
| Mounting Location | Wall |
| Degrees of Motion | -15/+15 Tilt; 180 Swivel |
| Distance from Wall (in.) | 12.7 |
| Distance from Wall (cm) | 32 |
| Distance from Wall (mm) | 323 |
| Minimum Screen Size (in.) | 23 |
| Minimum Screen Size (cm) | 58.4 |
| Maximum Screen Size (in.) | 55 |
| Maximum Screen Size (cm) | 139.7 |
| Maximum Weight Capacity (lbs.) | 51 |
| Maximum Weight Capacity (kg) | 23 |
| Min/Max Arm Extension (in.) | 2.83 min to 18.34 max |
| Min/Max Arm Extension (cm) | 71.9 min to 46.6 max |
| Number of Displays | 1 |
| Shipping Dimensions (hwd / in.) | 17.30 x 13.70 x 3.30 |
| Shipping Dimensions (hwd / cm) | 43.94 x 34.80 x 8.38 |
| Shipping Weight (lbs.) | 8.90 |
| Shipping Weight (kg) | 4.04 |

| | |
|--------------------------------------|---------------------------------|
| Unit Dimensions (hwd / in.) | 17.100 x 18.100 x 17.900 |
| Unit Dimensions (hwd / cm) | 16.69 x 6.88 x 63.19 |
| Unit Weight (lbs.) | 7.1 |
| Unit Weight (kg) | 3.22 |
| Assembly Required | Yes |
| FEATURES & SPECIFICATIONS | |
| Antimicrobial | No |
| Cord Management | Yes |
| Tools Necessary | Yes |
| Security Lock | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; RoHS3; CE (Europe); REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |