

## Outdoor Full-Motion TV Wall Mount with Fully Articulating Arm for 37" to 80" Flat-Screen Displays

MODEL NUMBER: DWM3780XOUT



Mounts your 37 to 80 in. television to the wall of your outdoor deck, balcony, patio or pool area to provide optimal viewing angles.

### Features

#### Outdoor TV Wall Mount Positions Your Monitor at the Perfect Viewing Angle

This VESA-compliant full-motion TV wall mount lets you place your outdoor display where everyone can see it best. It's ideal for not only digital signage, but also decks, balconies, patios, swimming pools and anywhere else people watch a television set or monitor outdoors. It fits most flat-panel TVs from 37 to 80 inches and supports up to 110 lbs (49.9 kgs).

#### Swivel and Tilt the Screen to Find the Perfect and Most Comfortable Viewing Angle

The full-motion articulating arm adjusts independently to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features  $-20^{\circ}$  to  $+10^{\circ}$  tilt and  $-90^{\circ}$  to  $+90^{\circ}$  swivel for positioning your screen just right. Easy  $-3^{\circ}$  to  $+3^{\circ}$  screen adjustment lets you quickly find just the right angle without interrupting your day.

#### VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this TV wall mount supports the following VESA mounting hole patterns: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400 and 600 x 400. Hardware for mounting on wood or concrete block is included.

#### Sure to Stand Up Against Weather and Other Outdoor Elements

The weatherproof steel frame, high-grade powder-coated finish, stainless steel hardware and wall plate covers are specifically designed to withstand the stress of repeated adjustments and outdoor use. Monitor cables clip to the arm to eliminate clutter and keep your outdoor setting organized.

### Highlights

- TV wall mount with articulating arm adjusts viewing angle easily with just a single touch
- $-20^{\circ}$  to  $+10^{\circ}$  tilt and  $-90^{\circ}$  to  $+90^{\circ}$  swivel helps you find the perfect angle to avoid glare
- Durable steel construction blends into any outdoor décor and supports up to 110 lbs (49.9 kgs)
- Display cables attach to arm to reduce clutter and keep cords organized
- VESA compliance ensures compatibility with most popular mounting hole patterns

### Applications

- Mounting a flat-screen television or monitor outside an office building, bar, restaurant, mall or anywhere else outdoor digital signage is desired
- Installing a TV in your patio or pool area that can be easily adjusted to accommodate the comfort levels of the audience

### System Requirements

- Flat-screen television or monitor from 37 to 80 in.

### Package Includes

- Mount assembly
- (2) Adapter brackets
- (2) Hex wrenches
- (2) Cable ties
- (4) M5 x 14 screws
- (4) M6 x 14 screws



- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (4) D6 washers
- (4) D8 washers
- (8) Small spacers
- (8) Large spacers
- (6) Tapping screws
- (6) Concrete anchors
- (6) Washers
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332258793
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Degrees of Motion	-20/+00 Tilt; 180 Swivel; -3/+3 Level Adjustment
Material of Construction	Steel
Maximum Screen Size (cm)	203
Maximum Screen Size (in.)	80
Maximum Weight Capacity (kg)	50
Maximum Weight Capacity (lbs.)	110
Min/Max Arm Extension (in.)	2.5 min to 20.1 max
Minimum Screen Size (cm)	93.9
Minimum Screen Size (in.)	37
Motion	Full
Mounting Location	Wall
Number of Displays	1
Shipping Dimensions (hwd / cm)	73.91 x 21.84 x 6.60
Shipping Dimensions (hwd / in.)	29.10 x 8.60 x 2.60
Shipping Weight (kg)	7.53



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Weight (lbs.)	16.60
Unit Dimensions (hwd / cm)	51.1 x 66 x 42.9
Unit Dimensions (hwd / in.)	20.1 x 26 x 16.9
Unit Weight (kg)	6.99
Unit Weight (lbs.)	15.4
VESA Pattern (mm)	200x200; 300x200; 400x200; 400x300; 400x400; 600x400
<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
<b>SPECIAL FEATURES</b>	
Cord Management	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	RoHS3, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>