

Swivel/Tilt Wall Mount for 60" to 100" TVs and Monitors, UL Certified

MODEL NUMBER: DWM60100XX



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

Description

The VESA-compliant DWM60100XX Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 60 to 100 inches.

The articulating arm has six pivots that adjust independently for angle to give you maximum flexibility in positioning your display to fit your environment and comfort level. A 90° swivel, -15° to +15° tilt and -3° to +3° screen level adjustment capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with scratch-resistant powder-coated finish supports up to 275 lbs (124.7 kgs).

Frame is open for easy wall access. Mounting hardware included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 200 x 500 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 300 x 500 mm, 300 x 600 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 400 x 500 mm, 400 x 600 mm, 500 x 200 mm, 500 x 300 mm, 500 x 400 mm, 500 x 500 mm, 500 x 600 mm, 600 x 300 mm, 600 x 400 mm, 600 x 500 mm, 600 x 600 mm, 600 x 900 mm, 700 x 300 mm, 700 x 400 mm, 700 x 500 mm, 700 x 600 mm, 800 x 400 mm, 800 x 500 mm, 800 x 600 mm, 900 x 500 mm, 900 x 600 mm

Features

Mounts Your TV or Monitor to the Wall Fits most flat-panel televisions, monitors and other displays from 60 to 100 in. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Articulated arm with 6 pivots adjusts independently for angle. Mounting hardware included. Tested in accordance with UL Standard 2442.

Convenient Adjustment 90° swivel, -15° to +15° tilt and -3° to +3° screen level adjustment capability provides comfortable viewing from multiple angles.

Durable Metal Construction Supports up to 275 lbs (124.7 kgs). Open frame allows easy wall access. Scratch-resistant powder-coated finish blends with any décor. Display cable attaches to mount to reduce clutter.

VESA Compliance Supports the following VESA mounting hole patterns: 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 200 x 500 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 300 x 500 mm, 300 x 600 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 400 x 500 mm, 400 x 600 mm, 500 x 200 mm, 500 x 300 mm, 500 x 400 mm, 500 x 500 mm, 500 x 600 mm, 600 x 300 mm, 600 x 400 mm, 600 x 500 mm,

Highlights

- Fits most flat-panel displays from 60 to 100 in.
- 90° swivel, -15° to +15° tilt and -3° to +3° screen adjustment
- Durable metal construction
- Supports up to 275 lbs (124.7 kgs)

Package Includes

- Wall mount
- Wall template
- (2) Wall brackets
- (4) Cable guides
- (4) M4 x 6 screws
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- (4) Anchor bolts
- (4) Concrete anchors
- (2) D8 washers
- Hex key
- Owner's manual

600 x 600 mm, 600 x 900 mm, 700 x 300 mm, 700 x 400 mm, 700 x 500 mm, 700 x 600 mm, 800 x 400 mm, 800 x 500 mm, 800 x 600 mm, 900 x 500 mm, 900 x 600 mm

Specifications

OVERVIEW	
UPC Code	037332186591
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	200x200; 200x300; 200x400; 200x500; 300x200; 300x300; 300x400; 300x500; 300x600; 400x200; 400x300; 400x400; 400x500; 400x600; 500x200; 500x300; 500x400; 500x500; 500x600; 600x300; 600x400; 600x500; 600x600; 600x900; 700x300; 700x400; 700x500; 700x600; 800x400; 800x500; 800x600; 900x500; 900x600
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 90 Swivel; -3/+3 Level Adjustment
Minimum Screen Size (in.)	60
Minimum Screen Size (cm)	152.4
Maximum Screen Size (in.)	100
Maximum Screen Size (cm)	254
Maximum Weight Capacity (lbs.)	275
Maximum Weight Capacity (kg)	125
Min/Max Arm Extension (in.)	2.76 min to 24.61 max
Min/Max Arm Extension (cm)	7.01 min to 62.51 max
Number of Displays	1
Shipping Dimensions (hwd / in.)	3.14 x 23.35 x 46.00
Shipping Dimensions (hwd / cm)	7.98 x 59.31 x 116.84
Shipping Weight (lbs.)	38.10
Shipping Weight (kg)	17.28
Unit Dimensions (hwd / in.)	24.200 x 36.500 x 24.620
Unit Dimensions (hwd / cm)	61.5 x 92.7 x 62.5
Unit Weight (lbs.)	31.50
Unit Weight (kg)	14.29
Assembly Required	Yes

FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 2442
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty