


## Heavy-Duty Tilt Wall Mount for 37" to 80" TVs and Monitors, Flat or Curved Screens, UL Certified

MODEL NUMBER: DWT3780XUL



Hangs a flat-panel or curved-screen television, monitor or other display on the wall. Recommended for home theaters, classrooms, boardrooms, hotels, bars and restaurants.

### Description

The VESA-compliant DWT3780XUL Heavy-Duty Tilt Wall Mount allows you to mount your flat-panel or curved-screen television, monitor or other display on the wall. Recommended for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most displays from 37 to 80 inches.

A -10° to 0° tilt capability minimizes glare and provides comfortable viewing from multiple angles.

Adjusting the tilt angle is simple using the easy-grip twin knobs located on the wall plate.

The mount is concealed behind the display to give a sleek, professional appearance. An open back enables easy access to cabling. Built-in bubble level allows accurate wall plate leveling. Durable all-metal frame with scratch-resistant powder-coated finish supports up to 165 lbs (74.8 kgs). Mounting hardware included.

Conforms to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 500 x 300 mm, 500 x 400 mm, 600 x 300 mm, 600 x 400 mm, 800 x 300 mm and 800 x 400 mm

This mount has been tested in accordance with UL Standard 2442.

### Features

**Mounts Your TV or Monitor to the Wall** Fits most flat-panel or curved-screen televisions, monitors and other displays from 37 to 80 in. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Mounts out of sight behind display for sleek, professional appearance. Mounting hardware included.

**Convenient Angle Adjustment** -10° to 0° tilt capability provides comfortable viewing from multiple angles. Improves viewing angles in applications where audience is below the display. Easy-grip knobs allow simple adjustment of tilt angle.

**Durable Metal Construction** Supports up to 165 lbs (74.8 kgs). Open architecture enables easy access to cabling. Built-in bubble level for accurate display leveling. Scratch-resistant powder-coated finish. Tested in accordance with UL Standard 2442.

**VESA Compliance** Supports the following VESA mounting hole patterns: 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 500 x 300 mm, 500 x 400 mm, 600 x 300 mm, 600 x 400 mm, 800 x 300 mm and 800 x 400 mm

### Highlights

- Fits most flat-panel or curved-screen displays from 37 to 80 in.
- Open architecture enables easy access to cabling
- -10° to 0° tilt capability for comfortable viewing
- Tested in accordance with UL Standard 2442
- Supports up to 165 lbs (74.8 kgs)

### Package Includes

- Wall plate
- (2) Adapter brackets
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (4) Washers
- (8) Small spacers
- (8) Big spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

## Specifications

OVERVIEW	
UPC Code	037332203991
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x300; 500x400; 600x300; 600x400; 800x300; 800x400
Motion	Tilt
Mounting Location	Wall
Degrees of Motion	-10/+0 Tilt
Distance from Wall (in.)	1.81
Distance from Wall (cm)	5
Distance from Wall (mm)	46
Minimum Screen Size (in.)	37
Minimum Screen Size (cm)	93.98
Maximum Screen Size (in.)	80
Maximum Screen Size (cm)	203.2
Maximum Weight Capacity (lbs.)	165
Maximum Weight Capacity (kg)	75
Number of Displays	1
Shipping Dimensions (hwd / in.)	2.40 x 8.90 x 35.20
Shipping Dimensions (hwd / cm)	6.10 x 22.61 x 89.41
Shipping Weight (lbs.)	8.50
Shipping Weight (kg)	3.86
Unit Dimensions (hwd / in.)	33.460 x 1.810 x 7.990
Unit Dimensions (hwd / cm)	85.1 x 4.6 x 20.3
Unit Weight (lbs.)	7.9
Unit Weight (kg)	3.58
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No



Powering Business Worldwide

TRIPP LITE  
SERIES

Cord Management	No
Tools Necessary	Yes
Security Lock	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 2442
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.