

Heavy-Duty Tilt Security TV Wall Mount for 45-55" TVs & Monitors - Flat Screen, Portrait Mode

MODEL NUMBER: DWTPSC4555M



Security wall mount with combination lock mounts your 45–55 in. flat-panel television or monitor to the wall in portrait mode.

Features

Portrait Wall Mount Hangs Your Flat-Panel TV or Monitor on the Wall Recommended for classrooms, conference rooms, hotels, bars, restaurants or anywhere else you may want to show off a television or monitor in portrait mode, this heavy-duty anti-theft TV wall mount is hidden out of sight behind the display for a sleek, professional appearance. It fits most flat-panel displays from 45 to 55 inches and up to 110 lbs (49.9 kgs). Mounting hardware is included.

Durable All-Metal Construction Provides Convenient Cable Access The tilt TV wall mount is constructed from heavy-duty steel with a powder-coated black finish that resists scratches. Rear openings with smooth edges enable easy access to cables. A built-in bubble level helps ensure your display is evenly mounted. The DWTPSC4555M is designed for portrait viewing, making it ideal for menus, schedules and announcements.

Designed to Keep Your Display Safe and Secure This security wall mount was conceived with your television or monitor's safety in mind, especially if the display is located in a public area with unguarded traffic, such as a library, classroom or hotel lobby. It comes with a solid steel security bar that slides through the mounting brackets and is secured into place with an included four-position combination lock.

Tilt Feature Lets You Adjust the Viewing Angle to Your Specifications You can adjust the horizontal angle of your display up to 10°. This will minimize glare on the screen and allow you to customize the angle for comfortable viewing.

Complies with VESA Standards VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing industry-wide standards for products like flat-panel TVs and monitors. To comply with these standards, most manufacturers use a series of universal mounting hole patterns, measured in millimeters, on the backs of the products. Measure the vertical and horizontal distances between the holes on the back of your display or refer to your display's owner's manual to find its VESA pattern. This monitor wall mount conforms to VESA-compliant displays with any of the following standard mounting hole patterns: 200 x 100, 200 x 200, 200 x 300, 200 x 400, 200 x 500, 300 x 200, 300 x 300, 300 x 400, 300 x 500, 300 x 600, 400 x 200, 400 x 300, 400 x 400, 400 x 500 and 400 x 600.

Highlights

- Accepts most popular flat-screen displays from 45 to 55 in. up to 110 lbs (49.9 kgs)
- Displays in portrait mode for easy reading of menus, schedules, announcements, etc.
- Solid steel security bar and included combo lock deters tampering and theft
- Open architecture and built-in level enable easy cable access and accurate leveling
- Tilts up to 10° to minimize glare and provide comfortable custom viewing angles

Applications

- Avoid theft by mounting a flat-screen monitor or TV to this secure mounting bracket with a solid steel security bar and lock
- Ideal for conference rooms, restaurants, hotels, classrooms, lobbies or anywhere else digital signage is needed

Package Includes

- Wall plate
- (2) Extension brackets
- (2) Adapter brackets
- Security bar
- (8) M6 x 6 screws
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws



- (4) Washers
- (8) Small spacers
- (8) Large spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- (2) D8 washers
- Safety pin
- Hex key
- Combination lock
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332238542
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
VESA Pattern (mm)	200x100; 200x200; 200x300; 200x400; 200x500; 300x200; 300x300; 300x400; 300x500; 300x600; 400x200; 400x300; 400x400; 400x500; 400x600
Distance from Wall (in.)	3.1
Distance from Wall (cm)	8
Distance from Wall (mm)	79
Material of Construction	Steel
Maximum Screen Size (cm)	139.7
Maximum Screen Size (in.)	55
Maximum Weight Capacity (kg)	50
Maximum Weight Capacity (lbs.)	110
Minimum Screen Size (in.)	45
Minimum Screen Size (cm)	114.3
Motion	Tilt
Mounting Location	Wall
Number of Displays	1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	7.87 x 24.13 x 55.12
Shipping Dimensions (hwd / in.)	3.10 x 9.50 x 21.70
Shipping Weight (kg)	5.58
Shipping Weight (lbs.)	12.30
Unit Dimensions (hwd / in.)	19.7 x 26.77 x 3.1
Unit Weight (kg)	4.49
Unit Weight (lbs.)	9.9
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
SPECIAL FEATURES	
Cord Management	No
Security Lock	Yes
STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>