


## Heavy-Duty Tilt Security Wall Mount for 32" to 55" TVs and Monitors, Flat or Curved Screens, UL Certified

MODEL NUMBER: DWTSC3255MUL



Security wall mount with combination lock mounts your flat-panel or curved-screen television or monitor to the wall.

### Features

**Security Wall Mount Hangs Your Flat-Panel or Curved-Screen TV or Monitor on the Wall**Ideal for home theaters, classrooms, conference rooms, hotels, bars, restaurants or anywhere else you may want to show off a television or monitor, this heavy-duty TV wall mount is hidden out of sight behind the display for a sleek, professional appearance. It fits most flat-panel or curved-screen displays from 32 to 55 inches and 99 pounds (44.9 kg). Mounting hardware is included. Function and weight tested in accordance with UL Standard 2442 up to 150 pounds (68 kg).

**Durable All-Metal Construction Provides Convenient Cable Access**The 55-inch-TV wall mount is constructed from heavy-duty steel with a powder-coated black finish that resists scratches. Rear openings with smooth edges enable easy access to cables. A built-in bubble level helps ensure your display is evenly mounted. This heavy-duty wall mount supports 99 pounds (44.9 kg) and is function and weight tested to 150 pounds (68 kg) in accordance with UL Standard 2442.

**Designed to Keep Your Display Safe and Secure**This heavy-duty wall mount was conceived with your television or monitor's security in mind, especially if the display is located in a public area with much unguarded traffic, such as a library, classroom or hotel lobby. It comes with a solid steel security bar that slides through the mounting brackets and is secured into place with an included three-position combination lock.

**Tilt Feature Lets You Adjust the Viewing Angle to Your Specifications**You can adjust the horizontal angle of your display from  $-15^{\circ}$  to  $+10^{\circ}$ . This will minimize glare on the screen and allow you to customize the angle for comfortable viewing.

**Complies with VESA Standards**VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing industry-wide standards for products like flat-panel TVs and monitors. To comply with these standards, most manufacturers use a series of universal mounting hole patterns, measured in millimeters, on the backs of the products. Measure the vertical and horizontal distances between the holes on the back of your display or refer to your display's owner's manual to find its VESA pattern. This 55-inch-TV wall mount conforms to VESA-compliant displays with any of the following standard mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300 and 400 x 400.

### Highlights

- Accepts most popular flat- or curved-screen displays from 32 to 55 in. 99 lbs (44.9 kgs)
- In addition, function and weight tested in accordance with UL standard 2442 up to 150 lbs (68 kgs)
- Solid steel security bar and included combo lock deters tampering and theft
- Heavy-duty steel construction designed for long life and to resist wear and tear
- Open architecture and built-in level enable easy cable access and accurate leveling
- Tilts  $-15^{\circ}$  to  $+10^{\circ}$  to minimize glare and provide comfortable custom viewing angles

### Applications

- Mounting a flat- or curved-screen television or monitor in an office lobby, conference room, bar, restaurant, airport or anywhere else digital signage is desired
- Securing an expensive display in a hotel lobby, classroom, library, hospital, truck stop or other public area with much foot traffic

### Package Includes

- Wall plate
- (2) Adapter brackets
- Security bar
- (2) End caps
- (4) End cap screws
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (4) Washers
- (8) Small spacers
- (8) Large spacers
- (4) Anchor bolts
- (4) Concrete anchors
- (4) 20 mm washers
- Combination lock
- Hex key



Powering Business Worldwide

TRIPP LITE  
SERIES

**5-Year Warranty and Environmentally Responsible Design**The DWTS3255MUL comes with a 5-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting commitment to environmental responsibility.

- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332213723
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400
Motion	Tilt
Mounting Location	Wall
Degrees of Motion	-15/+10 Tilt
Minimum Screen Size (in.)	32
Minimum Screen Size (cm)	81.28
Maximum Screen Size (in.)	55
Maximum Screen Size (cm)	139.7
Maximum Weight Capacity (lbs.)	150
Maximum Weight Capacity (kg)	68
Number of Displays	1
Shipping Dimensions (hwd / in.)	21.60 x 6.50 x 1.80
Shipping Dimensions (hwd / cm)	54.86 x 16.51 x 4.57
Shipping Weight (lbs.)	6.98
Shipping Weight (kg)	3.17
Unit Dimensions (hwd / in.)	20.300 x 17.300 x 2.300
Unit Dimensions (hwd / cm)	51.5 x 44.0 x 5.9
Unit Weight (lbs.)	5.20
Unit Weight (kg)	2.36
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes



Powering Business Worldwide

TRIPP LITE  
SERIES

Security Lock	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 2442
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.