

Universal Wall Bracket for Wireless Access Point with Cover - Right Angle, Steel, White

MODEL NUMBER: ENBRKTCVR



Durable steel bracket mounts your Wi-Fi access point (WAP) high on a wall to protect it from tampering and provide an optimum signal.

Features

Universal Wall-Mount Bracket Secures and Organizes Your Wireless Access Point

Protect your indoor Wi-Fi access point by mounting it high on a wall or ceiling, away from probing hands. This SmartRack® wall bracket is constructed from heavy-duty cold-rolled steel with a durable white powder-coated finish. It's recommended for offices, dorms, hotels, classrooms, small businesses and other indoor areas where you need to keep your WAP secure, organized and out of the way.

Accommodates a Wide Range of WAPs, Including Cisco and Aruba

The ENBRKTCVR fits most access-point bolt patterns and is compatible with Cisco low-profile and universal brackets. It also comes with a T-bar bracket for mounting Aruba and other WAP brands. Hardware is included for equipment installation. Open rear and side cutouts allow easy cable routing and reduce cable clutter. The durable wall bracket comes ready for horizontal or vertical mounting on a wall or ceiling with user-provided hardware.

Locks Securely to Help Prevent Damage, Tampering or Theft

This Wi-Fi access point enclosure features a protective steel cover. It locks securely with the included key to protect its contents against theft, tampering, dust and other contaminants.

Highlights

- Designed for Cisco (low-profile and universal), Aruba and most other WAP brands
- Installs high on a wall to protect router/modem/WAP from theft or tampering
- Heavy-duty steel bracket allows an optimum Wi-Fi signal in all directions
- Open rear and side cutouts allow easy access to data and power cabling
- Equipment-mounting hardware included; attaches to wall with user-provided hardware

Applications

- Mount a wireless access point high on a wall or ceiling to protect it from damage, theft or tampering
- Strengthen a wireless signal in another or a distant part of an office

Package Includes

- Wall bracket with cover
- T-bar bracket
- (4) #8-32 screws
- (2) #6-32 screws
- Cable tie
- Key
- Installation guide

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332214454
Rack Type	Open-Frame
PHYSICAL	
Color	White
Maximum Device Depth (cm)	22.86
Maximum Device Depth (in.)	9.00
Maximum Device Depth (mm)	229
Maximum Weight Capacity (kg)	5
Maximum Weight Capacity (lbs.)	10
Rack Height	0U
Shipping Dimensions (hwd / cm)	19.50 x 24.00 x 29.00
Shipping Dimensions (hwd / in.)	7.67 x 9.44 x 11.41
Shipping Weight (kg)	2.10
Shipping Weight (lbs.)	4.62
Unit Dimensions (cm)	12.8 x 18.7
Unit Dimensions (hwd / cm)	12.83 x 18.74 x 23.08
Unit Dimensions (hwd / in.)	5.050 x 7.378 x 9.087
Unit Dimensions (in.)	5.1 x 7.4
Unit Weight (kg)	1.41
Unit Weight (lbs.)	3.100
CERTIFICATIONS	
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>