

# RF Remote Control for Windows 7 & Vista

MODEL NUMBER: ER-V2



### Description

The RF Remote for Windows 7 & Vista is a sleek and powerful RF remote control designed specifically for use with Windows 7 & Vista's Media Center multimedia software. It provides more range, convenience and flexibility than infrared remotes.

### Features

- **Range:** The RF Remote for Windows Vista provides a range of up to 90-ft. (27.43 m) (about three times the distance of infrared remotes).
- **Convenience:** Unlike an infrared remote, this RF remote does not require line of sight to the RF receiver. This allows you to manage Media Center from more areas within the room or even from other areas of your house.
- **Flexibility:** Since the RF signal works through walls and furniture, you have more flexibility in locating the PC that will be used to run Media Center. For example, you can place the PC inside an entertainment center cabinet or within an AV closet and still easily control Media Center with the remote.

### Highlights

- Controls Media Center in Windows Vista and Windows 7
- Works through walls and furniture
- For Windows 7 and Vista Home Premium and Vista Ultimate

### System Requirements

Windows:

- An available USB port
- Windows 7 Home Premium or Ultimate (64-bit) & Windows Vista Home Premium or Windows Vista Ultimate (32bit or 64bit)
- TV tuner card with FM radio capability required for live TV and radio functionality

This remote control is designed specifically for use with Windows Vista Media Center.

### Package Includes

- RF Remote Control
- USB RF Receiver
- Printed Quick Start Guide
- Two AA batteries for remote

## Specifications

OVERVIEW	
UPC Code	672603045018
Model Frequency	433 Mhz
PRODUCT OVERVIEW	
Product Overview	Keyspan-by-Tripp Lite RF Remote for Windows Vista
PHYSICAL	
Color	Silver
Shipping Dimensions (hwd / in.)	9.00 x 6.30 x 1.75
Shipping Dimensions (hwd / cm)	22.86 x 16.00 x 4.44



Powering Business Worldwide



Shipping Weight (lbs.)	0.75
Shipping Weight (kg)	0.34
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	90
Signal Range (m)	27
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.