

## Easy Pull Long-Run Display Cable - Type-A Analog PVC Trunk Cable, 35 ft.

MODEL NUMBER: EZA-035



### Highlights

- Versatile trunk cable allows for a variety of connection options
- At a diameter of 7/8 in., it easily pulls through conduit or confined spaces using the included end cap with integrated pull tab
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200, as well as Audio pass through

### Package Includes

- Easy Pull Type-A VGA Analog PVC Trunk Cable, 35 ft.

### Description

Tripp Lite's EZA-035 35 ft. Easy Pull VGA Trunk Cable makes pulling video cable through conduit or confined areas a breeze. Threaded ends feature screw on pull-caps, which can be attached to fish tape. Choose from a variety of connector choices that easily screw on to the threaded ends of the trunk cable. Trunk cables are available in 35 ft., 50 ft. and 100 ft. lengths, both PVC and plenum rated. Cable ends are colored-coded green to denote VGA applications (Digital trunk cables are Yellow). Cable features triple-shielded construction with 75 ohm coax conductors for RGBHV signals supporting resolutions up to 1600 x 1200. Trunk also carries Audio signals when used with Easy Pull end kits that feature Audio connections.

### Features

- Eliminates the need to field terminate VGA connectors
- Detachable, screw-on connector with pull tab (7/8 in. diameter) makes it easy to pull through tight spaces, and helps protect the cable from strain, dirt, debris and damage when doing so
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Available in both PVC and Plenum versions
- Comes in 35 ft., 50 ft. and 100 ft. lengths
- Supports Video and Audio pass through depending on end kit used
- Choose from a variety of connector combinations for the perfect fit

## Specifications

OVERVIEW	
UPC Code	037332141903



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>INPUT</b>	
Cable Length (ft.)	35
Cable Length (m)	10.7
<b>PHYSICAL</b>	
Color	Black; Green
Shipping Dimensions (hwd / cm)	4.32 x 17.02 x 17.53
Shipping Dimensions (hwd / in.)	1.70 x 6.70 x 6.90
Shipping Weight (kg)	0.77
Shipping Weight (lbs.)	1.70
<b>CONNECTIONS</b>	
Side A - Connector 1	DIN 14 PIN (FEMALE)
Side B - Connector 1	DIN 14 PIN (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	VGA/SVGA
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>