

# Easy Pull Long-Run Display Cable - Type-A Analog Plenum Trunk Cable, 35 ft. (10.67 m)

MODEL NUMBER: EZA-035-P



## Highlights

- Versatile trunk cable allows for a variety of connection options
- Plenum-rated jacket to comply with local fire codes
- At a diameter of 7/8 in., it easily pulls through conduit or confined spaces using the included end cap with integrated pull tab
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200, as well as Audio pass through

## Package Includes

- Easy Pull Type-A VGA Analog Plenum Trunk Cable, 35 ft.

## Features

- Eliminates the need to field terminate VGA connectors
- Plenum-rated jacket to comply with local fire codes
- Detachable, screw-on connectors
- At a diameter of 7/8 in., it makes pulling long cables fast and easy
- Protects entire cable from strain, dirt, debris and damage
- Choose from a variety of connector combinations for the perfect fit
- Available in 35 ft., 50 ft. and 100 ft. lengths, both PVC and plenum rated
- Supports Video and Audio pass through depending on end kit used

## Specifications

OVERVIEW	
UPC Code	037332141873
Technology	VGA/SVGA
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DIN 14 PIN (FEMALE)
Side B - Connector 1	DIN 14 PIN (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black; Green



Powering Business Worldwide



Cable Jacket Color	Black; Green
Cable Length (ft.)	35
Cable Length (m)	10.67
Shipping Dimensions (hwd / in.)	1.00 x 8.00 x 8.00
Shipping Dimensions (hwd / cm)	2.54 x 20.32 x 20.32
Shipping Weight (lbs.)	1.90
Shipping Weight (kg)	0.86
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.