

Easy Pull Type-A Connectors - (F/F set of VGA with Audio and Faceplates)

MODEL NUMBER: EZA-VGAAF-2



Highlights

- SVGA / 3.5mm Stereo Connector Kit, Female to Female
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200
- Easily pull through conduit or confined spaces with included pull-caps

Package Includes

- 2 x HD15 Female w/stereo 3.5mm socket, 1-ft. (0.31 m) pigtail
- 2 x Mounting plate w/HD15 and 3.5mm cutouts

Features

- Eliminates the need to field terminate VGA connectors
- Wall plates with HD15 and 3.5mm stereo cut-outs cleanly finish off the cable run
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35 ft., 50 ft. and 100 ft. PVC lengths, and 35 ft. and 50 ft. Plenum jackets
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

Specifications

OVERVIEW	
UPC Code	037332142849
Technology	VGA/SVGA; Stereo Audio
PHYSICAL	
Color	Black; Green
Cable Length (ft.)	1
Cable Length (m)	0.30
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	0.35
Shipping Weight (kg)	0.16

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

CONNECTIONS	
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	3.5MM (FEMALE)
Side A - Connector 3	DIN 14 PIN (MALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	3.5MM (FEMALE)
Side B - Connector 3	DIN 14 PIN (MALE)
Latching or Gripping Connector	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

TRIPP-LITE

by **EAT•N**

© 2022 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.