

## Easy Pull Type-A Connectors - F/F set of VGA, 3.5mm, RCA Audio, Composite Video

MODEL NUMBER: EZA-VGACSAF-2



### Highlights

- SVGA / 3.5mm / Red-White RCA Audio / Composite Video, Female to Female
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

### Package Includes

2 x HD15/3.5mm/Red White RCA Audio/Composite Video, All female Jacks, with wallplates

### Description

Easy Pull Connector Kit includes: 2 x HD15 Female, 2 x stereo 3.5mm jack, 4 x RCA Red/White Audio jacks, and 2 x Yellow Composite Video jack, with 2 x faceplates and 1 ft. pigtails. Video support up to 1600 x 1200. Use with either PVC or Plenum Easy Pull trunk cables.

### Features

- Easy Pull, SVGA / 3.5mm / Red-White RCA Audio / Composite Video, Female to Female
- Eliminates the need to field terminate VGA connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35 ft., 50 ft. and 100 ft. lengths, PVC or Plenum rated jackets
- Support resolutions up to 1600 x 1200

## Specifications

| OVERVIEW           |              |
|--------------------|--------------|
| UPC Code           | 037332153784 |
| INPUT              |              |
| Cable Length (ft.) | 0.5          |
| Cable Length (m)   | 0.2          |
| PHYSICAL           |              |
| Color              | Black; Green |



|                                      |                                   |
|--------------------------------------|-----------------------------------|
| Shipping Dimensions (hwd / cm)       | 5.08 x 15.75 x 23.11              |
| Shipping Dimensions (hwd / in.)      | 2.00 x 6.20 x 9.10                |
| Shipping Weight (kg)                 | 0.36                              |
| Shipping Weight (lbs.)               | 0.80                              |
| <b>CONNECTIONS</b>                   |                                   |
| Side A - Connector 1                 | HD15 (FEMALE)                     |
| Side A - Connector 2                 | 3.5MM (FEMALE)                    |
| Side A - Connector 3                 | DIN 14 PIN (MALE)                 |
| Side B - Connector 1                 | HD15 (FEMALE)                     |
| Side B - Connector 2                 | 3.5MM (FEMALE)                    |
| Side B - Connector 3                 | DIN 14 PIN (MALE)                 |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                   |
| Technology                           | Composite; Stereo Audio; VGA/SVGA |
| <b>WARRANTY</b>                      |                                   |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty         |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>