

Easy Pull Type-A Connectors - (F/F set of VGA with Faceplates)

MODEL NUMBER: EZA-VGAF-2



Highlights

- SVGA Connector Kit, Female to Female -HD15, 2 x Wall plates
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200
- Easily pulls through conduit or confined spaces with included pull-caps

Package Includes

- Type-A Easy Pull Kit w/HD15 F/F, 1-ft. (0.31 m) pigtails & (2) Wall plates

Description

Easy Pull Connector Kit includes: 2 x HD15 Female - 1-ft. (0.31 m) pigtails and 2 Wall plates. Easy Pull trunk run with a finished appearance. Video support up to 1600 x 1200. Use with either PVC or Plenum trunk cables.

Features

- Eliminates the need to field terminate VGA connectors
- Wall plates with HD15 cut-out cleanly finishes off the cable run
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35-ft. (10.67 m), 50-ft. (15.24 m) and 100-ft. (30.5 m) PVC lengths, and 35-ft. (10.67 m) and 50-ft. (15.24 m) Plenum jackets
- Supports resolutions up to 1600 x 1200

Specifications

OVERVIEW	
UPC Code	037332142832
Product Type	Passive
Technology	VGA/SVGA
PHYSICAL	
Color	Black; Green
Cable Length (ft.)	1

Cable Length (m)	0.30
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	0.35
Shipping Weight (kg)	0.16
CONNECTIONS	
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	DIN 14 PIN (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	DIN 14 PIN (FEMALE)
Latching or Gripping Connector	No
FEATURES & SPECIFICATIONS	
IP68 Rated	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty