

Easy Pull Type-A Connectors - (M/F set of VGA with Faceplate)

MODEL NUMBER: **EZA-VGAX-2**



Highlights

- SVGA Connector Kit, Male to Female - HD15, Wall Plate
- Versatile trunk cable allows for a variety of connection options
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200

Package Includes

- HD15 Male 1 ft. pigtail
- HD15 Female 1 ft. pigtail
- Wall plate w/HD15 cut-outs

Description

Easy Pull Connector Kit includes: HD15 Male & HD15 Female - 1 ft. pigtail and Wall Plate. Completes your Easy Pull trunk run with a finished appearance. Video support up to 1600 x 1200. Use with either PVC or Plenum trunk cables.

Features

- Eliminates the need to field terminate VGA connectors
- Wall plate with HD15 cut-out cleanly finish off the cable run
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Trunk cables available in 35. ft, 50. ft, and 100 ft. PVC lengths, and 35 ft. and 50 ft. Plenum jackets
- Supports resolutions up to 1600 x 1200

Specifications

OVERVIEW	
UPC Code	037332141972
Technology	VGA/SVGA
Cable Type	Passive
PHYSICAL	
Color	Black; Green
Cable Length (ft.)	1
Cable Length (m)	0.30

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.05
Shipping Weight (kg)	0.02
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	DIN 14 PIN (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	DIN 14 PIN (FEMALE)
Latching or Gripping Connector	No
FEATURES & SPECIFICATIONS	
IP68 Rated	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.