

## FireWire IEEE 1394 Cable (6pin/6pin M/M) 6-ft.

MODEL NUMBER: **F005-006**



### Description

Tripp Lite's new Firewire series is a perfect compliment to your connectivity solutions. This 6 ft. IEEE-1394 Firewire cable has 6-pin male to 6-pin male connectors. It supports data transmission rates of 100~400Mbps and is most commonly used to connect a PC device to a PC device. Firewire cables have gold-plated connectors and gold-plated copper contacts for superior conductivity; premium double-shielded cable with both a braid and a foil shield to virtually eliminate crosstalk and reduce EMI/RFI interference.

### Features

- All Tripp Lite Firewire (IEEE 1394) cabling includes superior foil shielding for reliable error-free data communications.
- Firewire cable meets IEEE 1394 standards as set by the institute of electrical and electronic engineers.
- Premium quadruple-shielded cables with tinned copper braid and aluminum
- Mylar foil on each twisted pair as well as on the cable as a whole.
- Gold plated connectors provide superior conductivity.
- Supports data transmission of 100~400Mbps

## Specifications

| OVERVIEW           |              |
|--------------------|--------------|
| UPC Code           | 037332011961 |
| INPUT              |              |
| Cable Length (ft.) | 6            |

### Highlights

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole
- Gold plated connectors provide superior conductivity
- Retail packaging

### System Requirements

- Two Firewire IEEE 1394 devices each with 6 Pin Female connectors.

### Package Includes

- 6 Foot External Firewire (IEEE 1394) Cable 6 Pin to 6 Pin.



|                                      |                           |
|--------------------------------------|---------------------------|
| Cable Length (m)                     | 1.8                       |
| <b>PHYSICAL</b>                      |                           |
| Shipping Dimensions (hwd / in.)      | 9.00 x 7.00 x 0.50        |
| Shipping Dimensions (hwd / cm)       | 22.86 x 17.78 x 1.27      |
| Shipping Weight (lbs.)               | 0.23                      |
| Shipping Weight (kg)                 | 0.10                      |
| Color                                | Black                     |
| <b>CONNECTIONS</b>                   |                           |
| Side A - Connector 1                 | 6 PIN (MALE)              |
| Side B - Connector 1                 | 6 PIN (MALE)              |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                           |
| Technology                           | FireWire                  |
| <b>CERTIFICATIONS</b>                |                           |
| Certifications                       | RoHS-Compliant            |
| <b>WARRANTY</b>                      |                           |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty |

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>