

## FireWire IEEE 1394 Cable (6pin/6pin M/M) 15 ft. (4.57 m)

MODEL NUMBER: **F005-015**

### Highlights

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole
- Gold plated connectors provide superior conductivity

### System Requirements

- Two Firewire IEEE 1394 devices each with 6 Pin Female connectors.

### Package Includes

- 15-ft. Firewire IEEE 1394 6Pin/6Pin with Gold Connectors

### Features

- All Firewire (IEEE 1394) cabling includes superior foil shielding for reliable error-free data communications.
- Firewire cable meets IEEE 1394 standards as set by the institute of electrical and electronic engineers.
- Premium quadruple-shielded cables with tinned copper braid and aluminum
- Mylar foil on each twisted pair as well as on the cable as a whole.
- Gold plated connectors provide superior conductivity.
- Supports data transmission of 100~400Mbps

## Specifications

OVERVIEW	
UPC Code	037332011985
Technology	FireWire
CONNECTIONS	
Side A - Connector 1	6 PIN (MALE)
Side B - Connector 1	6 PIN (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	15
Cable Length (m)	4.57



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.51
Shipping Weight (kg)	0.23
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.