

## FireWire IEEE 1394 Cable (6pin/6pin M/M) 15-ft.

MODEL NUMBER: **F005-015**



### Description

Tripp Lite's new Firewire series is a perfect compliment to your connectivity solutions. this 15 ft. IEEE-1394 Firewire cable has 6-pin male to 6-pin male connectors supports data transmission of 100~400Mbps and used most commonly to connect a PC device to a PC device. Firewire cables have gold-plated connectors and gold-plated copper contacts for superior conductivity. Premium double-shielded cable with both a braid and a foil shield to virtually eliminate crosstalk and reduce EMI/RFI interference.

### Features

- All Tripp Lite Firewire (IEEE 1394) cabling includes superior foil shielding for reliable error-free data communications.
- Firewire cable meets IEEE 1394 standards as set by the institute of electrical and electronic engineers.
- Premium quadruple-shielded cables with tinned copper braid and aluminum
- Mylar foil on each twisted pair as well as on the cable as a whole.
- Gold plated connectors provide superior conductivity.
- Supports data transmission of 100~400Mbps

## Specifications

OVERVIEW	
UPC Code	037332011985
INPUT	
Cable Length (ft.)	15
Cable Length (m)	4.6

### Highlights

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole
- Gold plated connectors provide superior conductivity

### System Requirements

- Two Firewire IEEE 1394 devices each with 6 Pin Female connectors.

### Package Includes

- 15-ft. Firewire IEEE 1394 6Pin/6Pin with Gold Connectors



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.51
Shipping Weight (kg)	0.23
Color	Black
<b>CONNECTIONS</b>	
Side A - Connector 1	6 PIN (MALE)
Side B - Connector 1	6 PIN (MALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	FireWire
<b>CERTIFICATIONS</b>	
Certifications	RoHS-Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>