

FireWire 800 IEEE 1394b Hi-speed Cable (9pin/9pin M/M) 10 ft. (3.05 m)

MODEL NUMBER: F015-010



Highlights

- Twice the Speed of Original FireWire - Data Transfers to 800Mbps
- Meets FireWire 800 and 1394b Specifications
- Backward compatible to Original FireWire components

Package Includes

- 10-ft. (3.05 m) IEEE-1394b FireWire 800 Gold Hi-Speed 9pin/9pin Cable

Features

- Data transfer rates to 800Mbps
- Hot Pluggable - supports Plug-n-Play operation
- Premium triple-shielded cable with molded, Gold connectors
- Backward compatible with original FireWire systems and devices
- Compatible with PC, Mac, SUN, and other IEEE-1394b equipped systems

Specifications

| OVERVIEW | |
|---------------------------------|----------------------|
| UPC Code | 037332124616 |
| Technology | FireWire |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Length (ft.) | 10 |
| Cable Length (m) | 3.05 |
| Shipping Dimensions (hwd / in.) | 0.50 x 5.10 x 8.60 |
| Shipping Dimensions (hwd / cm) | 1.27 x 12.95 x 21.84 |
| Shipping Weight (lbs.) | 0.20 |
| Shipping Weight (kg) | 0.09 |

| ENVIRONMENTAL | |
|-------------------------------------|------------------------------|
| Operating Temperature Range | 32° to 104°F (0° to 40°C) |
| Storage Temperature Range | -14° to 131°F (-25° to 55°C) |
| Relative Humidity | 5 to 90 % |
| CONNECTIONS | |
| Side A - Connector 1 | 9 PIN (MALE) |
| Side B - Connector 1 | 9 PIN (MALE) |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |